

23 x 20mm FL, Grade 1, Double-Convex Lens



Stock **#74-324** CLEARANCE **3 In Stock**

-

1

+

€10^{,25}

ADD TO CART

Volume Pricing	
Qty 1+	€10,25 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

Physical & Mechanical Properties

	Diameter (mm):
23.00	

Optical Properties

	Effective Focal Length EFL (mm):
20.00	

Regulatory Compliance

	Certificate of Conformance:
--	-----------------------------

Product Details

- Ideal for Experimenting and Prototyping Applications
- Quantities Extremely Limited, Buy While Supplies Last
- For Even More Deals, Check out [Mega Clearance: Optics](#)

Double-convex (DCX) lenses have two outward curved surfaces, a positive focal length and are useful for 1:1 imaging and in multi-element systems.

50mm and Larger Experimental Quality Double-Convex (DCX) Lenses are offered in several experimental grade options. Grade 1 is standard optical glass, edged, free of visible scratches, chips, stains, or oxidation. Grade 2 is unedged, non-optical glass, small chips, slight stains, or other defects. They may have slight edge cement separation.

Note: Specifications for experimental grade optics may vary as much as 10% from those listed. Also, no additional information is available other than what is provided.

Technical Information

