

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 575nm CWL, 25mm Dia. Hard Coated OD 4.0 25nm Bandpass Filter



Stock #87-790 3-4 DAYS

[Additional Bandwidths](#)



1



€246,00

ADD TO CART

Qty 1-5

€246,00

Qty 6+

€193,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.1

Angle of Incidence (°):
0

Bandwidth (nm):

20
Optical Density OD (Average): ≥4.0
Clear Aperture CA (mm): 21.0
Center Wavelength CWL (nm): 575.00 ±3
Center Wavelength CWL Tolerance (nm): ±3
Full Width-Half Max FWHM (nm): 25.00 ±3
Full Width-Half Max FWHM Tolerance (nm): ±3
Substrate: ☐ Optical Glass
Minimum Transmission (%): >90
Coating: Hard Coated
Thickness with Mount (mm): 5.00
Surface Quality: 80-50
Type: Bandpass Filter
Typical Applications: Bo-Pro 3, KFP-Red
Blocking Wavelength Range (nm): 200 - 1200
Construction: Mounted in Black Anodized Ring
Environmental Durability: Humidity per MIL-STD-810H, Section 507.6 Temperature per MIL-STD-810H, Section 501.7 and 502.7
Physical Durability: Adhesion per MIL-PRF-13830B, Section C.4.5.12 Moderate abrasion per MIL-PRF-13830B, Section C.4.5.11 Cleaning per MIL-C-48497A Section 4.5.4.2
Mount Thickness (mm): 5.0 ±0.1
Substrate Thickness (mm): 3.5 ±0.5

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant