

TECHSPEC® 5mm Dia. x 25mm FL 1064nm V-Coat, Fused Silica PCX Lens



Stock **#34-132** 3-4 DAYS

[Other Coating Options](#)



1



€126,00

ADD TO CART

Qty 1-5

€126,00

Qty 6+

€100,75

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
5.00 +0.0/-0.025

Effective Focal Length EFL (mm):

25.00 @ 587.6nm
Back Focal Length BFL (mm): 23.97
Coating: Laser V-Coat (1064nm)
Coating Specification: R _{abs} <0.25% @ 1064nm
Substrate: ☐ Fused Silica (Corning 7980)
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): ≤1
Center Thickness CT (mm): 1.50 ±0.05
Edge Thickness ET (mm): 1.5
Radius R₁ (mm): 11.46
Clear Aperture CA (mm): 4.5
f/#: 5.00
Numerical Aperture NA: 0.10
Design Wavelength DWL (nm): 1064
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Edges: Fine Ground, Protective Bevel as Needed
Damage Threshold, By Design: ☐ 5 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant