

5mm FL Ultra High Resolution Fixed Focal Length Lenses



#68-681

Stock **#68-681** 6 In Stock

-

1

+

€2.043⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€2.043,00 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Series:

Ultra High Resolution Fixed Focal Length Lenses

Type:

Fixed Focal Length Lens

Physical & Mechanical Properties

Iris Option:

Variable

Length (mm):

57.10	
48.0	Maximum Diameter (mm):
48	Outer Diameter (mm):
120.00	Weight (g):

Optical Properties

142.5	Field of View @ Min Working Distance (mm):
142.5mm - 64.9°	Horizontal Field of View, 1/2" Sensor:
11.00	Maximum Image Circle (mm):
5.00	Focal Length FL (mm):
100 - ∞	Working Distance (mm):
f/1.8 - f/16	Aperture (f/#):
<-0.33%	Maximum Distortion (%):
VIS	Lens Wavelength Range:

Sensor

2/3"	Maximum Sensor Format:
2.40	Pixel Size (µm):

Threading & Mounting

M46 x0.75	Filter Thread:
C-Mount	Mount:

Regulatory Compliance

Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	REACH 241:

Product Details

- 2/3", C-Mount Lens
- Up to 10 MegaPixels, 2.4µm Pixel Size Sensors
- Spectral Range of 400 - 1000nm
- 5mm to 50mm Focal Lengths

Ultra High Resolution Fixed Focal Length Lenses are designed to provide 10 MegaPixel resolution on axis. These lenses have a spectral range of 400 to 1000nm. Through the use of a floating focus and aspheric lens elements, these high-resolution lenses are able to maintain excellent performance from 100mm to infinity. Ultra High Resolution Fixed Focal Length Lenses feature locking focus, iris rings, and a front filter thread to allow the use of standard optical filters for increased versatility. The lenses are available in 7 focal length options and feature very low distortion.