

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 5mm Dia. X 15mm FL, NIR I Coated, Double-Convex Lens



Stock #63-628 ☒ In Stock

☐ [Other Coating Options](#)



1



€49,50

ADD TO CART

Qty 1-9

€49,50

Qty 10+

€44,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
5.00 +0.0/-0.025

Back Focal Length BFL (mm):

14.33
Effective Focal Length EFL (mm): 15.00
Coating: NIR I (600-1050nm)
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 2.00
Center Thickness Tolerance (mm): ±0.05
Edge Thickness ET (mm): 1.58
Radius R₁=R₂ (mm): 15.16
Clear Aperture CA (mm): 4.5
f/#: 3.00
Focal Length Specification Wavelength (nm): 587.6
Numerical Aperture NA: 0.17
Type: Double-Convex Lens
Wavelength Range (nm): 600 - 1050
Damage Threshold, By Design: ☐ 7 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant