

## 6" Length, 1/4-20 and 1/4-20, Steel Post



Stock #72-797 NEW 9 In Stock

⊖ 1 ⊕ €8.<sup>50</sup>

ADD TO CART

Volume Pricing	
Qty 1+	€8,50 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

English Type:

### Physical & Mechanical Properties

12.7 Diameter (mm):

0.5 Diameter (inches):

152.4 Length (mm):

## Threading & Mounting

Thread 1: 1/4 - 20  
Thread 2: 1/4 - 20

### Male Thread:

## Regulatory Compliance

[Compliant](#)

### RoHS 2015:

[View](#)

### Certificate of Conformance:

[Compliant](#)

### Reach 247:

## Product Details

- English or Metric Versions Options Available
- Wide Variety of Lengths Available from 25.4 to 304.8mm (1" to 12").
- Removable Top and Bottom Set Screws Available

Stainless Steel Optical Mounting Posts are a practical and straightforward way to integrate optical assemblies and photonic equipment onto an [optical lab table](#) or [breadboard](#). All mounting posts are 12.7 mm (0.5") in diameter and are offered in various lengths from 25.4 to 304.8mm (1" to 12"). Each mounting post features a female thread on each end with a set screw preinstalled, making it simple to mount components with counterbore or tapped hole mounting features. Stainless Steel Optical Mounting Posts can be used with [Post Holders](#) to allow for height adjustment of the optical component, and for a secure connection with the optical benchtop. Thread values (M4 x 0.7/M6 x 1.0 for Metric; 8-32<sup>1/4</sup>-20 for English) are laser-engraved on the ends of each post for quick identification and integration.

**Note:** All posts have a through-hole that allows an Allen wrench, 5.5mm or 7/32" key size, or other tools to rotate the post easily.