

[See all 68 Products in Family](#)

TECHSPEC[®] 6.0mm Dia. x -12 FL, Uncoated, UV Plano-Concave Lens



UV Fused Silica Plano-Concave (PCV) Lenses



Stock **#45-698** **20+ In Stock**

[Other Coating Options](#)

-

1

+

€121^{.00}

ADD TO CART

Volume Pricing	
Qty 1-5	€121,00 each
Qty 6-25	€97,00 each
Qty 26-49	€91,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Plano-Concave Lens

Type:

Max. Flat Annulus is 0.3mm

Note:

Physical & Mechanical Properties	
Diameter (mm):	6.00 +0.0/-0.025
Center Thickness CT (mm):	2.00
Center Thickness Tolerance (mm):	±0.05
Centering (arcmin):	<1
Clear Aperture CA (mm):	5.4
Edge Thickness ET (mm):	2.71


Optical Properties	
Effective Focal Length EFL (mm):	-12.00
Substrate: ☐	Fused Silica (Corning 7980)
f/#:	2.00
Numerical Aperture NA:	0.25
Coating:	Uncoated
Wavelength Range (nm):	200 - 2200
Back Focal Length BFL (mm):	-13.38
Focal Length Specification Wavelength (nm):	587.6
Focal Length Tolerance (%):	±1
Radius R ₁ (mm):	-5.50
Surface Quality:	40-20
Power (P-V) @ 632.8nm:	1.5λ
Irregularity (P-V) @ 632.8nm:	λ/4


Regulatory Compliance	
RoHS 2015:	Compliant
Reach 223:	Compliant
Certificate of Conformance:	View

Product Details






- Negative Focal Lengths for Beam Expansion or Light Projection Applications
 - Wavelength Range of 200 - 2200nm
 - Popular UV-AR Coating Option Available
- TECHSPEC® UV Fused Silica Plano-Concave (PCV) Lenses are high performance UV optic elements, manufactured utilizing state of the art CNC equipment. Zygo’s GPI-XP Interferometer is used to assure the surface accuracy and performance of these UV optics. UV Grade lenses are precision manufactured using research-grade synthetic fused silica. In addition to providing excellent transmission characteristics and higher operating temperatures, synthetic fused silica also exhibits an exceptional inclusion specification and chemical purity. TECHSPEC® UV Fused Silica Plano-Concave (PCV) Lenses are an ideal choice for many laser and imaging applications, particularly those involving ultraviolet wavelengths. A broadband anti-reflection coating is available for optimized throughput in the ultraviolet spectrum.




Technical Information





FUSED SILICA																											
Uncoated Fused Silica Typical Transmission <table><caption>Uncoated Fused Silica Typical Transmission Data (Approximate)</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>93</td></tr><tr><td>400</td><td>94</td></tr><tr><td>600</td><td>94</td></tr><tr><td>800</td><td>94</td></tr><tr><td>1000</td><td>94</td></tr><tr><td>1200</td><td>94</td></tr><tr><td>1400</td><td>92</td></tr><tr><td>1600</td><td>94</td></tr><tr><td>1800</td><td>94</td></tr><tr><td>2000</td><td>94</td></tr><tr><td>2200</td><td>90</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	200	93	400	94	600	94	800	94	1000	94	1200	94	1400	92	1600	94	1800	94	2000	94	2200	90	Typical transmission of a 3mm thick, uncoated fused silica window across the UV - NIR spectra. Click Here to Download Data		
Wavelength (nm)	Transmission T (%)																										
200	93																										
400	94																										
600	94																										
800	94																										
1000	94																										
1200	94																										
1400	92																										
1600	94																										
1800	94																										
2000	94																										
2200	90																										
Fused Silica with MgF₂ Coating Typical Transmission <table><caption>Fused Silica with MgF₂ Coating Typical Transmission Data (Approximate)</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>94</td></tr><tr><td>400</td><td>97</td></tr><tr><td>600</td><td>97</td></tr><tr><td>800</td><td>96</td></tr><tr><td>1000</td><td>96</td></tr><tr><td>1200</td><td>96</td></tr><tr><td>1400</td><td>93</td></tr><tr><td>1600</td><td>95</td></tr><tr><td>1800</td><td>95</td></tr><tr><td>2000</td><td>95</td></tr><tr><td>2200</td><td>90</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	200	94	400	97	600	97	800	96	1000	96	1200	96	1400	93	1600	95	1800	95	2000	95	2200	90	Typical transmission of a 3mm thick fused silica window with MgF₂ (400-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 1.75\% @ 400 - 700\text{nm}$ (N-BK7) Data outside this range is not guaranteed and is for reference only. Click Here to Download Data		
Wavelength (nm)	Transmission T (%)																										
200	94																										
400	97																										
600	97																										
800	96																										
1000	96																										
1200	96																										
1400	93																										
1600	95																										
1800	95																										
2000	95																										
2200	90																										
Fused Silica with UV-AR Coating Typical Transmission <table><caption>Fused Silica with UV-AR Coating Typical Transmission Data (Approximate)</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>70</td></tr><tr><td>250</td><td>98</td></tr><tr><td>300</td><td>99</td></tr><tr><td>400</td><td>100</td></tr><tr><td>500</td><td>98</td></tr><tr><td>600</td><td>90</td></tr><tr><td>700</td><td>80</td></tr><tr><td>800</td><td>75</td></tr><tr><td>900</td><td>75</td></tr><tr><td>1000</td><td>75</td></tr><tr><td>1100</td><td>76</td></tr><tr><td>1200</td><td>77</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	200	70	250	98	300	99	400	100	500	98	600	90	700	80	800	75	900	75	1000	75	1100	76	1200	77	Typical transmission of a 3mm thick fused silica window with UV-AR (250-425nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 1.0\% @ 250 - 425\text{nm}$ $R_{avg} \leq 0.75\% @ 250 - 425\text{nm}$ $R_{avg} \leq 0.5\% @ 370 - 420\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Wavelength (nm)	Transmission T (%)																										
200	70																										
250	98																										
300	99																										
400	100																										
500	98																										
600	90																										
700	80																										
800	75																										
900	75																										
1000	75																										
1100	76																										
1200	77																										
Fused Silica with UV-VIS Coating Typical Transmission																											

	Typical transmission of a 3mm thick fused silica window with UV-VIS (250-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 1.0\%$ @ 350 - 450nm $R_{avg} \leq 1.5\%$ @ 250 - 700nm Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Fused Silica with VIS-EXT Coating Typical Transmission 	Typical transmission of a 3mm thick fused silica window with VIS-EXT (350-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.5\%$ @ 350 - 700nm Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Fused Silica with VIS-NIR Coating Typical Transmission 	Typical transmission of a 3mm thick fused silica window with VIS-NIR (400-1000nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 0.25\%$ @ 880nm $R_{avg} \leq 1.25\%$ @ 400 - 870nm $R_{avg} \leq 1.25\%$ @ 890 - 1000nm Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Fused Silica with VIS 0° Coating Typical Transmission 	Typical transmission of a 3mm thick fused silica window with VIS 0° (425-675nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.4\%$ @ 425 - 675nm Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Fused Silica with YAG-BBAR Coating Typical Transmission 	Typical transmission of a 3mm thick fused silica window with YAG-BBAR (500-1100nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification:

	The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 0.25\%$ @ 532nm $R_{abs} \leq 0.25\%$ @ 1064nm $R_{avg} \leq 1.0\%$ @ 500 - 1100nm Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Fused Silica with NIR I Coating Typical Transmission 	Typical transmission of a 3mm thick fused silica window with NIR I (600 - 1050nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.5\%$ @ 600 - 1050nm Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Fused Silica with NIR II Coating Typical Transmission 	Typical transmission of a 3mm thick fused silica window with NIR II (750 - 1550nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 1.5\%$ @ 750 - 800nm $R_{abs} \leq 1.0\%$ @ 800 - 1550nm $R_{avg} \leq 0.7\%$ @ 750 - 1550nm Data outside this range is not guaranteed and is for reference only. Click Here to Download Data

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts