

TECHSPEC<sup>®</sup> 6.35mm Dia. 266nm 45°, Nd:YAG Laser Line Mirror



TECHSPEC<sup>®</sup> Nd:YAG Laser Line Mirrors

Stock **#38-829** 11 In Stock

-

1

+

€114<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | €114,00 each                  |
| Qty 6-25       | €99,00 each                   |
| Need More?     | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

| General                          |                       |
|----------------------------------|-----------------------|
| Laser Mirror                     | Type:                 |
| Physical & Mechanical Properties |                       |
| <3                               | Parallelism (arcmin): |
| 85                               | Clear Aperture (%):   |

|                                                                          |                                                       |
|--------------------------------------------------------------------------|-------------------------------------------------------|
| Commercial Polish                                                        | Back Surface:                                         |
| 6.35 +0.00/-0.10                                                         | Diameter (mm):                                        |
| 4.00 ±0.20                                                               | Thickness (mm):                                       |
| Optical Properties                                                       |                                                       |
| 10-5                                                                     | Surface Quality:                                      |
| 99.5                                                                     | Reflection at DWL (%):                                |
| R <sub>abs</sub> >99.5% @ 266nm<br>R <sub>avg</sub> >99.5% @ 263 - 268nm | Coating Specification:                                |
| 263 - 268                                                                | Wavelength Range (nm):                                |
| λ/10                                                                     | Surface Flatness (P-V):                               |
| Dielectric                                                               | Coating Type:                                         |
| Laser Mirror (263-268nm)                                                 | Coating:                                              |
| 266                                                                      | Design Wavelength DWL (nm):                           |
| 45                                                                       | Angle of Incidence (°):                               |
| <a href="#">Fused Silica</a> (Corning 7980)                              | Substrate: <input type="checkbox"/>                   |
| 2.5 J/cm <sup>2</sup> @ 266nm, 20ns, 20Hz                                | Damage Threshold, Reference: <input type="checkbox"/> |
| Regulatory Compliance                                                    |                                                       |
| <a href="#">View</a>                                                     | Certificate of Conformance:                           |

## Product Details

- Up to 99.9% Reflectivity at Nd:YAG Harmonic Frequencies
- High Laser Induced Damage Threshold Specifications
- 10-5 Surface Quality for Reduced Scatter in Sensitive Laser Applications
- [TECHSPEC® Laser Mirror Substrates](#) and [TECHSPEC® Yb:YAG Laser Line Mirrors](#) Also Available

TECHSPEC® Nd:YAG Laser Line Mirrors combine high reflectivity, excellent surface quality, and precision surface flatness to meet the requirements of demanding Nd:YAG laser applications. Each coating design has been tested to ensure a high laser damage threshold for compatibility with pulsed laser systems. These fused silica substrate laser mirrors have excellent thermal stability and are available in round, square, and rectangular profiles. TECHSPEC® Nd:YAG Laser Line Mirrors are ideal for laboratories and integration into larger laser systems. 266nm, 355nm, 532nm, 1064nm, and multi-line Nd:YAG mirror coatings are available.

**Note:** Contact us for customizable wavelengths, sizes, and varying AOI versions.

## Compatible Mounts