

TECHSPEC[®] 60mm Thick Inner Spacer Tube



TECHSPEC Multi-Element Spacer Ring



Stock **#11-207** **3 In Stock**

-

1

+

€95^{.00}

ADD TO CART

Volume Pricing	
Qty 1-4	€95,00 each
Qty 5-9	€83,90 each
Qty 10+	€77,80 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Spacer Ring

Function:

Physical & Mechanical Properties

60.00	Thickness (mm):
28.05	Outer Diameter (mm):
25	Inner Diameter (mm):

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:

Product Details

- Thicknesses Ranging from 0.1mm to 60mm
- Combine Parts of Different Thickness to Create Optimal Spacing
- Dull Black Finish to Reduce Stray Light
- Click [Here](#) to See How to Use the Multi-Element Tube System Components to Build an Optical System.

TECHSPEC® Multi-Element Spacer Rings and Spacer Tubes provide an easy method for controlling optical spacing within [TECHSPEC® Multi-Element Outer Tubes](#). Utilizing different combinations of ring and tube thicknesses provides for creating the optimal optical spacing for your application. These spacing elements feature a dull black coating to reduce unwanted internal stray light. TECHSPEC® Multi-Element Spacer Rings and Spacer Tubes are an essential component for any optical system requiring precision spacing of optical elements. Spacer Tubes with a thickness of 10mm or more have an internal baffle thread for a highly anti-reflective effect, further reducing undesired stray light.

Note: The TECHSPEC Spacer Ring Kit ([#11-193](#)) and TECHSPEC Spacer Tube Kit ([#11-208](#)) provide EO's full range of spacing capabilities for a reduced price.