

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 6.25mm Dia. X 10mm FL, VIS-NIR, Inked, Achromatic Lens



Stock #49-303-INK 3-5 DAYS
[Other Coating Options](#)

1 €82,00

ADD TO CART

Qty 1-5
€82,00

Qty 6+
€65,50

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
6.25 ±0.025

Effective Focal Length EFL (mm):

10.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 7.83
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 5.625
Centering (arcmin): <3
Center Thickness CT (mm): 4.09 ±0.10
Center Thickness CT 1 (mm): 3.06 ±0.05
Center Thickness CT 2 (mm): 1.03 ±0.05
Radius R ₁ (mm): 6.98
Radius R ₂ (mm): -4.35
Radius R ₃ (mm): -41.01
Edge Thickness ET (mm): 3.23
Substrate: ☐ N-BAF10 / N-SF10
Surface Quality: 40-20
f/#: 1.6
Numerical Aperture NA: 0.31
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @400 - 870nm R _{avg} ≤1.25% @890 - 1000nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 1000

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View