


TECHSPEC® 6.25mm UV Enhanced Aluminum Coated, N-BK7 Right Angle Prism



Stock **#24-177** [CONTACT US](#)

- 1 + **€75,00**

ADD TO CART

Qty 1-5
€75,00

Qty 6+
€60,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Flatness (P-V):
λ/4

Substrate:
[N-BK7](#)

Surface Quality:
60-40

Length of Legs (mm): 6.25
Dimensional Tolerance (mm): ±0.1
Coating Specification: R_{avg} >85% @ 250 - 700nm R_{avg} >89% @ 250 - 450nm
Coating: Enhanced Aluminum (250-700nm)
Coating Type: Metal
Angle Tolerance (arcmin): ±2
Bevel: Protective bevel as needed
Clear Aperture CA (mm): 7.96 x 5.63
Length of Hypotenuse (mm): 8.80
Type: Right Angle Mirror
Wavelength Range (µm): 0.25 - 0.7
Wavelength Range (nm): 250 - 700
Damage Threshold, Reference: ☐ 0.5 J/cm² @ 355nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant