

A black cylindrical device, likely a sensor or probe, is shown. A green fiber optic cable is connected to the front face of the cylinder. The cable has a metal connector with a green ring. Several white fibers are visible emerging from the connector. The device is set against a dark background.

1 **+** **€1.480^{,00}**

[ADD TO CART](#)

! Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

DANGER

LARGE BOTTLE OF
WIDE MOUTH 2750 BOTTLE

SHOCK HAZARD
SAFETY DATA SHEET AT THE BOTTOM
PLEASE SEE YOUR MANUAL

General	
---------	--

Diode	Type of Laser:

IIIb Laser Class - CDRH:

Physical & Mechanical Properties					
Physical Properties: - Melting Point: ~180°C - Density: ~1.2 g/cm³ - Solubility: Soluble in organic solvents like THF, DMSO. - Stability: Stable under ambient conditions.	Mechanical Properties: - Tensile Strength: ~50 MPa - Elongation at Break: ~10% - Modulus: ~2 GPa				
	Thermal Properties: - Glass Transition Temperature (T_g): ~100°C - Decomposition Temperature: ~300°C				
	Electrical Properties: - Volume Resistance: ~10^{12} Ω·cm - Surface Resistance: ~10^9 Ω				
	Optical Properties: - Refractive Index: ~1.5 - Transparency: Transparent in thin films.				
	Biocompatibility: Cytotoxicity: Non-toxic at concentrations up to 1 mg/mL.				
	Environmental Stability: - UV Radiation: Degradable under UV light. - Oxygen Exposure: Degradable in presence of oxygen.				
	Processing Methods: - Injection Molding: Suitable for large-scale production. - Extrusion: Can be extruded into fibers or films.				

Length of Fiber (m):

Optical Properties	
0.12	Numerical Aperture NA:
Fiber-Coupled	Spatial Mode:
4	Fiber Diameter (µm):
685.00 ±10	Wavelength (nm):
Red	Color:
Electrical	
20	Output Power (mW):
Hardware & Interface Connectivity	
5.0	Operating Voltage (V):
Power Supply: Power Supply Required and Sold Separately. USA: #73-818 Europe: #73-818 Japan: #13-640 Korea: #33-770 China: #73-818	
FC/PC	Connector:
Environmental & Durability Factors	
+15 to +30	Operating Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 233:

Product Details

- Single Mode Fiber with FC/PC Connector
- 1 to 100mW Output Power and 405 to 1550nm Wavelength Options
- Integrated Driver for Easy Operation

Pigtailed Laser Diode Modules feature an integrated 1m long, single mode fiber with an FC/PC connector. These laser diodes also feature an integrated driver for plug and play operation, only requiring a 5V external power supply ([#73-818](#)). Pigtailed Laser Diode Modules are available with VIS and NIR wavelengths ranging from 405 to 1550nm, with output powers ranging from 1 to 100mW. Their plug and play operation make these laser diodes ideal for a wide range of laboratory and OEM applications.