

TECHSPEC<sup>®</sup> 6mm Dia. x -9mm FL, VIS-NIR Coated, Double-Concave Lens



Stock **#48-941** [CONTACT US](#)

[Other Coating Options](#)

-

1

+

€46<sup>.50</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | €46,50 each                   |
| Qty 10-25      | €41,75 each                   |
| Qty 26-49      | €37,25 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:  
Double-Concave Lens

Physical & Mechanical Properties

|                      |                                  |
|----------------------|----------------------------------|
| 6.00 +0.0/-0.025     | Diameter (mm):                   |
| Protective as needed | Bevel:                           |
| 1.00                 | Center Thickness CT (mm):        |
| ±0.05                | Center Thickness Tolerance (mm): |
| <3                   | Centering (arcmin):              |
| 5.4                  | Clear Aperture CA (mm):          |
| 1.79                 | Edge Thickness ET (mm):          |

Optical Properties

|                                                                                                                    |                                                       |
|--------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------|
| -9.00                                                                                                              | Effective Focal Length EFL (mm):                      |
| N-BK7                                                                                                              | Substrate: <input type="checkbox"/>                   |
| 1.5                                                                                                                | f/#:                                                  |
| 0.33                                                                                                               | Numerical Aperture NA:                                |
| VIS-NIR (400-1000nm)                                                                                               | Coating:                                              |
| 400 - 1000                                                                                                         | Wavelength Range (nm):                                |
| -9.32                                                                                                              | Back Focal Length BFL (mm):                           |
| R <sub>abs</sub> ≤0.25% @ 880nm<br>R <sub>avg</sub> ≤1.25% @ 400 - 870nm<br>R <sub>avg</sub> ≤1.25% @ 890 - 1000nm | Coating Specification:                                |
| 587.6                                                                                                              | Focal Length Specification Wavelength (nm):           |
| ±1                                                                                                                 | Focal Length Tolerance (%):                           |
| -9.47                                                                                                              | Radius R <sub>1</sub> =R <sub>2</sub> (mm):           |
| 40-20                                                                                                              | Surface Quality:                                      |
| 5 J/cm² @ 532nm, 10ns                                                                                              | Damage Threshold, By Design: <input type="checkbox"/> |
| 1.5λ                                                                                                               | Power (P-V) @ 632.8nm:                                |
| λ/4                                                                                                                | Irregularity (P-V) @ 632.8nm:                         |

Regulatory Compliance


|           |                             |
|-----------|-----------------------------|
| Compliant | RoHS 2015:                  |
| View      | Certificate of Conformance: |
| Compliant | Reach 235:                  |

## Product Details

- AR Coated to Provide <1.25% Reflectance per Surface for 400 - 1000nm
- <0.25% Reflectance @ 880nm
- Designed for 0° Angle of Incidence
- Various Coating Options: [Uncoated](#), [VIS-EXT](#), [MgF<sub>2</sub>](#), [VIS 0°](#), [NIR I](#), and [NIR II](#)

TECHSPEC® VIS-NIR Coated Double-Concave (DCV) Lenses are designed to have two inward curved surfaces and a negative focal length similar to Plano-Concave (PCV) lenses. These lenses can be used for balancing aberrations created by other lenses within a system due to their negative spherical aberration. Double-Concave (DCV) lenses are commonly used in a variety of applications including image reduction, beam expansion and telescopes. TECHSPEC® VIS-NIR Coated Double-Concave (DCV) Lenses are optimized for transmission (>99%) in the near-infrared. These lenses are also available [Uncoated](#), [VIS-EXT](#), [MgF<sub>2</sub>](#), [VIS 0°](#), [NIR I](#), or with [NIR II](#) AR coating options.

## Technical Information



## Coating Curves

### Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Compatible Mounts