

TECHSPEC® 70mm, 120mm Radius, Metric Goniometer



TECHSPEC® Goniometers



Stock #66-535 3-4 DAYS

- 1 + €689,00

ADD TO CART

Qty 1-2

€689,00

Qty 3+

€600,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Goniometer

Type of Drive:
Lead Screw

Type: Metric
Stage Size (mm): 70 x 70
Travel (°): ±10
Construction: Aluminium Stage
Leadscrew Pitch (mm): 0.5
Load Capacity (kg): 6
Mounting Threads: (9) M6 x 1, (4) M3 x 0.5, (8) M2 x 0.4
Radius R (mm): 120
Resolution (arcmin): 5
Stage Size (inches): 2.75 x 2.75
Weight (kg): 0.3

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant