

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



TECHSPEC® Goniometers



Stock #66-537

CONTACT US



1



€727,00

ADD TO CART

Qty 1-2

€727,00

Qty 3+

€636,60

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Goniometer

Type of Drive:
Lead Screw

Type: Metric
Stage Size (mm): 70 x 70
Travel (°): ±8
Construction: Aluminium Stage
Leadscrew Pitch (mm): 0.5
Load Capacity (kg): 6
Mounting Threads: (9) M6 x 1, (4) M3 x 0.5, (8) M2 x 0.4
Radius R (mm): 180
Resolution (arcmin): 5
Stage Size (inches): 2.75 x 2.75
Weight (kg): 0.3

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant