

70mm MikroMak™ Prime Probe Lens



MikroMak™ Prime Probe Lenses



Stock **#16-131** 1 In Stock

-

1

+

€3.010⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€3.010,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:

Variable Magnification Lens

Physical & Mechanical Properties

Length (mm):

176.50

Maximum Diameter (mm):

48.00	
Optical Properties	
43.30	Maximum Image Circle (mm):
0X - 5.5X	Primary Magnification PMAG:
27 - ∞	Working Distance (mm):
Sensor	
35mm (43.3mm Image Circle)	Maximum Sensor Format:
Threading & Mounting	
M42 x0.75 (T-Mount)	Mount:
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 224:
View	Certificate of Conformance:

Product Details

- Designed for Use from Macro to Infinity
- Ideal for Industrial and Cinema Production Applications
- Excellent Sharpness Over Depth of Field
- [MikroMak™ PetzVex™ Prime Probe Lenses](#) Also Available

MikroMak™ Prime Probe Lenses, part of Infinity Photo-Optical Company's line of Nelsonian™ Optics, offer unparalleled depth of field, providing excellent clarity in applications requiring micro, macro, or infinity focus. When set to infinity, everything up to a close proximity of the MikroMak Prime Probe Lenses is automatically in focus. The knurled focus ring can then be used to adjust the focus of the lens to the micro or macro range, indicated by magnification markings on the lens body. MikroMak Prime Probe Lenses provide the flexibility required for creative story telling in photography and cinema production applications while providing the high performance required for industrial and laboratory use.

MikroMak Prime Probe Lenses are available in five different focal lengths: 40, 50, 70, 90, and 125mm. The 40 and 50mm lenses provide wide field images with moderate macro magnifications up to 1.75X (50mm) or 2X (40mm). The 40mm lens can be converted to have a 25mm focal length with 1X magnification through an adapter (sold separately). The 70, 90, and 125mm lenses provide high magnification and resolutions typical of objectives used on standard laboratory microscopes with a maximum magnification of 5.5X (70 and 125mm) or 6X (90mm). A suite of accessories including adapters to C-Mount, L-Mount, and Sony mounts, mounting solutions, spacers, and gears for motorization are available; see each specific accessory for more information.

Visit the [Infinity Photo-Optical Cinema Products](#) brand page to learn more about these products!