


[See all 32 Products in Family](#)

**TECHSPEC® 70R/30T 12.5 x 12.5mm, UV Plate Beamsplitter**



TECHSPEC® UV Plate Beamsplitters

Stock #84-485 **16 In Stock**

⊖ 1 ⊕ €126<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	€126,00 each
Qty 6-25	€100,00 each
Qty 26-99	€91,50 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Standard Beamsplitter **Type:**

**Physical & Mechanical Properties**

>85 **Clear Aperture (%):**

**Construction:**

Plate	
12.5 x 12.5 +0.00/-0.20	<b>Dimensions (mm):</b>
<5	<b>Parallelism (arcmin):</b>
2.00 ±0.38	<b>Thickness (mm):</b>
<b>Optical Properties</b>	
45	<b>Angle of Incidence (°):</b>
<b>Coating Specification:</b>	
Surface 1: $R_{\text{abs}} = 70 \pm 5\%$ @ 350nm, $R_{\text{avg}} = 70 \pm 10\%$ over 250 - 450nm	
$T_{\text{abs}} = 30 \pm 5\%$ @ 350nm, $T_{\text{avg}} = 30 \pm 10\%$ over 250 - 450nm	
Surface 2: BBAR ( $R_{\text{avg}} < 1\%$ , $R_{\text{abs}} < 2\%$ over 250 - 450nm)	
70/30	<b>Reflection/Transmission Ratio (R/T):</b>
<a href="#">Fused Silica</a> (Coming 7980)	<b>Substrate:</b> <input type="checkbox"/>
1λ	<b>Surface Flatness (P-V):</b>
60-40	<b>Surface Quality:</b>
250 - 450	<b>Wavelength Range (nm):</b>

<b>Regulatory Compliance</b>	
<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 235:</b>

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Multiple Transmission/Reflection Ratios Available
- BBAR Coated Second Surface
- Fused Silica Substrate

TECHSPEC® UV Plate Beamsplitters offer optimum performance in the 250-450nm spectral range and feature low absorption and negligible ghost reflections. The precision fused silica substrate has been designed to minimize the additional optical path length a beamsplitter adds to an imaging or photonic system. Available in multiple transmission/reflection ratios, TECHSPEC® UV Plate Beamsplitters are ideal for fluorescence imaging, biomedical and pharmaceutical applications, forensics, and spectroscopy. All coatings are designed for 45° AOI and random polarization.

## Compatible Mounts