

[See all 293 Products in Family](#)

TECHSPEC<sup>®</sup> 75mm Dia. x 300 mm FL, VIS 0°, Inked, Achromatic Lens



Stock **#88-594-INK** [CONTACT US](#)

☐ [Other Coating Options](#)

-

1

+

€398<sup>.00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | €398,00 each                  |
| Qty 6-25       | €319,00 each                  |
| Qty 26-49      | €299,00 each                  |
| Need More?     | <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Achromatic Lens

Type:

Physical & Mechanical Properties

|                      |                             |
|----------------------|-----------------------------|
| 75.00 ±0.025         | Diameter (mm):              |
| 73.5                 | Clear Aperture CA (mm):     |
| <1                   | Centering (arcmin):         |
| 19.59 ±0.20          | Center Thickness CT (mm):   |
| 13.59 ±0.10          | Center Thickness CT 1 (mm): |
| 6.00 ±0.10           | Center Thickness CT 2 (mm): |
| 13.97                | Edge Thickness ET (mm):     |
| Protective as needed | Bevel:                      |

|                                      |                                             |
|--------------------------------------|---------------------------------------------|
| Optical Properties                   |                                             |
| 300.00                               | Effective Focal Length EFL (mm):            |
| ±1                                   | Focal Length Tolerance (%):                 |
| 290.62                               | Back Focal Length BFL (mm):                 |
| 587.6                                | Focal Length Specification Wavelength (nm): |
| 184.05                               | Radius R <sub>1</sub> (mm):                 |
| -137.34                              | Radius R <sub>2</sub> (mm):                 |
| -399.33                              | Radius R <sub>3</sub> (mm):                 |
| N-BK7 / N-SF5                        | Substrate: <input type="checkbox"/>         |
| 40-20                                | Surface Quality:                            |
| 4.00                                 | f/#:                                        |
| 0.13                                 | Numerical Aperture NA:                      |
| VIS 0° (425-675nm)                   | Coating:                                    |
| R <sub>avg</sub> ≤0.4% @ 425 - 675nm | Coating Specification:                      |
| 1.5λ                                 | Power (P-V) @ 632.8nm:                      |
| λ/4                                  | Irregularity (P-V) @ 632.8nm:               |
| 425 - 675                            | Wavelength Range (nm):                      |

|                       |                             |
|-----------------------|-----------------------------|
| Regulatory Compliance |                             |
| View                  | Certificate of Conformance: |

## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Designed for 0° Angle of Incidence
- Less Than 0.4% Reflectance Per Surface from 425 - 675nm
- **MgF<sub>2</sub>** and **VIS-NIR** Coated Achromats Also Available

TECHSPEC® VIS 0° Coated Achromatic Lenses consist of two optical components cemented together to form an achromatic doublet. The doublet is computer optimized to correct for on-axis spherical and chromatic aberrations. Achromatic lenses are best for applications involving multi-color (white light) imaging due to their specific doublet lens pairing that enables them to correct the color separation inherent in glass. TECHSPEC® VIS 0° Coated

Technical Information



Coating Curves