

[See all 130 Products in Family](#)

TECHSPEC® 76.2mm Dia. 532nm 0-45°, Nd:YAG Laser Line Mirror



TECHSPEC® Nd:YAG Laser Line Mirrors



Stock #20-422 **3 In Stock**

⊖ 1 ⊕ €750.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	€750,00 each
Qty 6-25	€675,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Lasers Mirror **Type:**

Physical & Mechanical Properties

Parallelism (arcmin):

<3

90	Clear Aperture (%) :
M10	Back Surface :
76.20 +0.00/-0.10	Diameter (mm) :
12.70 ±0.20	Thickness (mm) :
Optical Properties	
10-5	Surface Quality :
99.8	Reflection at DWL (%) :
Coating Specification: R _{abs} >99.8% @ 532nm @ 0-45° AOI	
M10	Surface Flatness (P-V) :
Dielectric	Coating Type :
Laser Mirror (532nm)	Coating :
532	Design Wavelength DWL (nm) :
0-45	Angle of Incidence (°) :
Fused Silica (Corning 7980)	Substrate: <input type="checkbox"/>
Damage Threshold, By Design: <input type="checkbox"/> 10.0 J/cm ² @ 532nm, 20ns, 20Hz 1MW/cm ² @ 532nm	

Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Up to 99.9% Reflectivity at Nd:YAG Harmonic Frequencies
- High Laser Induced Damage Threshold Specifications
- 10-5 Surface Quality for Reduced Scatter in Sensitive Laser Applications
- [TECHSPEC® Laser Mirror Substrates](#) and [TECHSPEC® Yb:YAG Laser Line Mirrors](#) Also Available

TECHSPEC® Nd:YAG Laser Line Mirrors combine high reflectivity, excellent surface quality, and precision surface flatness to meet the requirements of demanding Nd:YAG laser applications. Each coating design has been tested to ensure a high laser damage threshold for compatibility with pulsed laser systems. These fused silica substrate laser mirrors have excellent thermal stability and are available in round, square, and rectangular profiles. TECHSPEC® Nd:YAG Laser Line Mirrors are ideal for laboratories and integration into larger laser systems. 266nm, 355nm, 532nm, 1064nm, and multi-line Nd:YAG mirror coatings are available.

Note: Contact us for customizable wavelengths, sizes, and varying AOI versions.

Compatible Mounts