See all 130 Products in Family

TECHSPEC® 76.2mm Dia. 266nm 0-45°, Nd:YAG Laser Line Mirror

TECHSPEC® Nd:YAG Laser Line Mirrors

Stock **#20-418** CONTACT US

- 1 + **€750**.00

ADD TO CART

Volume Pricing	
Qty 1-5	**€750,00** each
Qty 6-25	**€675,00** each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:

Laser Mirror

Physical & Mechanical Properties

Parallelism (arcmin):

<3

Clear Aperture (%):
90

Back Surface:
λ/10

Diameter (mm):
76.20 +0.00/-0.10

Thickness (mm):
12.70 ±0.20

Optical Properties

Surface Quality:
10-5

Reflection at DWL (%):
99.8

Coating Specification:
R_{abs} >99.8% @ 266nm @ 0-45° AOI

Surface Flatness (P-V):
λ/10

Coating Type:
Dielectric

Coating:
Laser Mirror (266nm)

Design Wavelength DWL (nm):
266

Angle of Incidence (°):
0-45

Substrate:
Fused Silica (Corning 7980)

Damage Threshold, By Design:
2.0 J/cm^2 @ 266nm, 20ns, 20Hz
1MW/cm^2 @ 266nm

Regulatory Compliance

Certificate of Conformance:
View

Product Details

- Up to 99.9% Reflectivity at Nd:YAG Harmonic Frequencies
- High Laser Induced Damage Threshold Specifications
- 10-5 Surface Quality for Reduced Scatter in Sensitive Laser Applications
- TECHSPEC® Laser Mirror Substrates and TECHSPEC® Yb:YAG Laser Line Mirrors Also Available

TECHSPEC® Nd:YAG Laser Line Mirrors combine high reflectivity, excellent surface quality, and precision surface flatness to meet the requirements of demanding Nd:YAG laser applications. Each coating design has been tested to ensure a high laser damage threshold for compatibility with pulsed laser systems. These fused silica substrate laser mirrors have excellent thermal stability and are available in round, square, and rectangular profiles. TECHSPEC® Nd:YAG Laser Line Mirrors are ideal for laboratories and integration into larger laser systems. 266nm, 355nm, 532nm, 1064nm, and multi-line Nd:YAG mirror coatings are available.

Note: Contact us for customizable wavelengths, sizes, and varying AOI versions.

Compatible Mounts

;