

[See all 39 Products in Family](#)

830nm High Performance Laser Line Filter 25mm Dia.



High Performance Laser Line Bandpass Filters

Stock **#64-259** **1 In Stock**

[Additional Bandwidths](#)

€852.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€852,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Bandpass Filter **Type:**

Physical & Mechanical Properties

25.00 +0.0/-0.1 **Diameter (mm):**

≥22 **Clear Aperture CA (mm):**

±0.10 **Thickness Tolerance (mm):**

Mounted in Black Anodized Ring **Construction:**

ML-C-48497A Paragraphs 4.5.3.1, 4.5.3.2, 4.5.3.3, 4.5.4.2, and 4.5.5.3 **Physical Durability:**

2.0 ±0.1 **Substrate Thickness (mm):**

Optical Properties

0 ±2 **Angle of Incidence (°):**

3.2 **Bandwidth (nm):**

<11 **Beam Deviation (arcsec):**

639 - 822 & 838 - 1325 **OD 5 Blocking Wavelength Range (nm) :**

764 - 818 & 843 - 913 **OD 6 Blocking Wavelength Range (nm):**

≥6.0 **Optical Density OD (Average):**

830.00 **Center Wavelength CWL (nm):**

830 **Design Wavelength DWL (nm):**

3.15 - 5.81 **Full Width-Half Max FWHM (nm):**

Fused Silica **Substrate:**

>90 **Minimum Transmission (%):**

Hard Coated **Coating:**

60-40 **Surface Quality:**

>90 **Transmission (%):**

639 - 822 & 838 - 1325 **Blocking Wavelength Range (nm):**

¼ @ 633nm **Transmitted Wavefront, P-V:**

Threading & Mounting

3.5 ±0.1 **Mount Thickness (mm):**

Environmental & Durability Factors

<5 **Temperature Dependence (ppm/°C):**

ML-STD-810F Paragraphs 501.4, 502.4, and 507.4 **Environmental Durability:**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[Compliant](#) **Reach 209:**

[View](#) **Certificate of Conformance:**







Product Details

- Over 90% Transmission at Specified Laser Lines
- Hard Coated Design
- Designed for Laser Applications

Available for use with common gas and solid state lasers, High Performance Laser-Line Bandpass Filters are designed to offer maximum transmission of stimulated emission, while eliminating noisy spontaneous emission. These laser line filters are available at popular diode and Nd:YAG laser lines, including 532nm, 785nm, and 1064nm. High Performance Laser-Line Bandpass Filters are ideal for laser-based fluorescence instrumentation, Raman spectroscopy, or for analytical or medical laser systems. Due to their steep edges, High Performance Laser-Line Bandpass Filters are excellent complements to TECHSPEC® Notch Filters and [Laser Line Longpass Filters](#).

Note: These filters are optimized for high spectral performance rather than high Laser Induced Damage Thresholds (LIDT). Atypical LIDT for these filters is 0.1 J/cm² @ 532nm, 10ns.

Technical Information



Compatible Mounts
