

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

LightPath 354220 | 780nm Alignment, 0.25 NA Fiber Collimator w/ FC/PC Connector

See More by [Lightpath®](#)



Fiber Optic Collimator and Focuser Assemblies



Stock #47-219 3-4 DAYS



1



€180,00

ADD TO CART

Qty 1-10

€180,00

Qty 11+

€158,50

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Effective Focal Length EFL (mm):
11.00 @ 633nm

Numerical Aperture NA:
0.25

Substrate: D-ZK3
Coating: BBAR (600-1050nm)
Coating Specification: Rabs <1.0% @ 600 - 1050nm
Surface Quality: 40-20
Clear Aperture CA (mm): 5.50
f#: 2.00
Bevel: Protective bevel as needed
Connector: FC/PC
Construction: 304L Stainless Steel Housing
Housing Diameter (mm): 11.00
Housing Length (mm): 17.1
Lightpath Lens Code: 354220
Mount: M11 x0.5
Type: Fiber Collimator
Wavelength Range (nm): 600 - 1050
Conjugate Distance: Infinite
Lens Included: #87-118
Alignment Wavelength (nm): 780

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant