

[See all 5 Products in Family](#)

# 850nm, UltraSeal Washdown Spot Light

See More by [Advanced Illumination](#)



Advanced Illumination High Intensity UltraSeal Washdown Spot Lights

Stock **#21-974** CLEARANCE **1 In Stock**

-

 1 

+

**€1.475<sup>.00</sup>**

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | €1.475,00 each                |
| Need More?     | <a href="#">Request Quote</a> |

**i** Prices shown are exclusive of VAT/local taxes

**Note:** This item requires accessories for use | [Learn More](#)

## Product Downloads

| General      |                       |
|--------------|-----------------------|
|              | Model Number:         |
| SL316M-850IC |                       |
|              | LED Lifetime (hours): |
| 50,000       |                       |
|              | Number of LEDs:       |
| 25           |                       |

|                       |                       |
|-----------------------|-----------------------|
| LED Illuminator       | Type of Illumination: |
| Advanced Illumination | Manufacturer:         |
| Spot Light            | Geometry:             |

|          |                    |
|----------|--------------------|
| Constant | Illumination Mode: |
|----------|--------------------|

Physical & Mechanical Properties

|     |             |
|-----|-------------|
| 290 | Weight (g): |
|-----|-------------|

Optical Properties

|    |        |
|----|--------|
| IR | Color: |
|----|--------|

|     |                  |
|-----|------------------|
| 850 | Wavelength (nm): |
|-----|------------------|

Hardware & Interface Connectivity

|              |            |
|--------------|------------|
| Flying Leads | Connector: |
|--------------|------------|

|                                                                                                                                                                                                                     |               |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|
| Power Supply Required and Sold Separately:<br>USA: <a href="#">#66-855</a><br>Europe: <a href="#">#66-855</a><br>Japan: <a href="#">#89-513</a><br>Korea: <a href="#">#33-773</a><br>China: <a href="#">#66-855</a> | Power Supply: |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|

|   |                      |
|---|----------------------|
| 2 | Length of Cable (m): |
|---|----------------------|

Environmental & Durability Factors

|          |                             |
|----------|-----------------------------|
| 0 to +60 | Operating Temperature (°C): |
|----------|-----------------------------|

Regulatory Compliance

|                      |                             |
|----------------------|-----------------------------|
| <a href="#">View</a> | Certificate of Conformance: |
|----------------------|-----------------------------|

## Product Details

- IP69K Certified for Extreme Washdown Environments
- Ideal for Hygienic and Aseptic Manufacturing Applications
- Intensity of Over 60,000 Lux at 300mm Working Distance

Advanced Illumination High Intensity UltraSeal Washdown Spot Lights are ideal for extreme environments including high pressure steam cleaning and prolonged liquid immersion. Available in five colors, these spot lights feature high intensity output and consistent uniformity. These spot lights are IP69K certified and their proprietary nickel finish ensures better thermal conductivity than stainless steel while the sealed design reduces the potential for material buildup and improves cleanability. Advanced Illumination High Intensity UltraSeal Washdown Spot Lights can be used in hygienic inspection environments, aseptic manufacturing, and food and beverage applications.