

[See all 8 Products in Family](#)

8° Viewing Angle, 515nm Compact Laser Driven Light Sources



Stock #72-532 **1 In Stock**

⊖ 1 ⊕ €565.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	€565,00 each
Qty 5-9	€508,50 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

14000 (L90) **Operating Lifetime (hours):**

MonaLIGHT B01 515nm **Model Number:**

Spot Light **Geometry:**

Physical & Mechanical Properties

12.00 **Diameter (mm):**

18.0 **Weight (g):**

Optical Properties

Green **Color:**

515 **Wavelength (nm):**

900 - 1100 **Luminous Flux (Lumens):**

8° **Viewing Angle (FWHM):**

up to 6000 cd **Peak Intensity:**

34° **Beam Angle (FWTM):**

Electrical

12.9 **Power Consumption (W):**

2.3 W (Maximum) **Output Power (W):**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- Compact With Luminous Flux up to 1300 Lumens (lm)
- 515 – 555nm Wavelength Options Available
- Long Bulb Lifetime of 14,000 Hours

Crytur MbnalIGHT Compact Laser Driven Light Sources are compact and versatile noncoherent light sources designed for modular integration into scientific or industrial applications. These light sources modules offer service lifetimes up to 14,000 hours and are available in three configurations; A01, B01, and F01. The MbnalIGHT A01 series feature asymmetric light output, a viewing angle of 38°, a luminous flux of 1000 – 1300 lm, wavelengths of 515, 535, 540, or 555nm and are ideal for applications requiring slit illumination. The MbnalIGHT B01 series are designed to provide a high output symmetrical beam, a viewing angle of 8°, a luminous flux of 900 – 1100 lm, in wavelengths of either 515nm or 540nm, and are ideal for integration into systems where customized light guides are required. The MbnalIGHT F01 series are ideal for direct fiber coupling and optical microscopy applications in which a low etendue is desirable, and offer a viewing angle of 5°, a luminous flux of 550 lm, and in wavelengths of either 515nm or 540nm. Crytur MbnalIGHT Compact Laser Driven Light Sources are designed for simple integration, with S-Mount (M12 x 0.5) threading on the housing, and bare lead connections for flexible power delivery. Typical applications for these light sources include; scientific research, biotech instrumentation, fluorescence microscopy, high-speed machine vision, endoscopy, and sensorics.

Note: Requires a power supply compatible with bare leads electronics