

8mm 2 MegaPixel Fixed Focal Length Lens



8mm Fixed Focal Length, #14-396

Stock **#14-396** 1 In Stock

-

1

+

€406⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€406,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Fixed Focal Length Lens

Type:

Physical & Mechanical Properties

Variable

Iris Option:

38.50

Length (mm):

Maximum Diameter (mm):

32.5	
	Weight (g):
107	
Optical Properties	
Horizontal Field of View @ Max Sensor Format:	
43.8°	
Horizontal Field of View, 1/2" Sensor:	
43.8°	
Horizontal Field of View, 1/3" Sensor:	
33.4°	
Horizontal Field of View, 1/4" Sensor:	
25.36°	
Maximum Image Circle (mm):	
8.00	
Focal Length FL (mm):	
8.00	
Working Distance (mm):	
100 - ∞	
Aperture (f/#):	
f/1.4 - f/16	
Distortion (%):	
<-0.7	
Lens Wavelength Range:	
VIS	
Sensor	
Maximum Sensor Format:	
1/2"	
Threading & Mounting	
Filter Thread:	
M30.5 x 0.50 (Female)	
Mount:	
C-Mount	
Regulatory Compliance	
Certificate of Conformance:	
View	

Product Details

- 2 MegaPixel Resolution Design
 - Lockable, Manual Focus and Iris
 - Fixed Focal Lengths from 4 to 50mm
 - C-Mount Lens Mount
- 2 MegaPixel Fixed Focal Length Lenses are designed for machine vision applications that require higher resolution than the [MegaPixel Fixed Focal Length Lenses](#). These C-Mount lenses feature built-in locking mechanisms for the manual focus and iris, preventing unwanted adjustments. Lenses with a fixed focal length from 4 to 50mm are available with the 6 to 50mm lenses featuring M30.5 x 0.5 filter thread, allowing the use of [machine vision filters](#). 2 MegaPixel Fixed Focal Length Lenses cover ½" and 2/3" sensor sizes, making them compatible with all of our [2MP machine vision cameras](#). These lenses are used in industrial machine vision, [factory automation](#), and factory inspection applications.