

TECHSPEC[®] 8.0mm Diameter, N-BK7 Ball Lens



TECHSPEC[®] N-BK7 Ball Lenses

Stock **#32-747** 20+ In Stock

-

1

+

€51⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	€51,00 each
Qty 11-25	€46,00 each
Qty 26-49	€43,50 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Ball Lens	Type:
Physical & Mechanical Properties	
8.00	Diameter (mm):
	Diameter Tolerance (µm):

±5.0	
Optical Properties	
N-BK7	Substrate: ☐
Uncoated	Coating:
350 - 2200	Wavelength Range (nm):
1.517	Index of Refraction (n _d):
0.625	Sphericity (μm):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- Can be Used as Fiber Coupling Spheres or Collimating Lenses
 - Ideal Pre-Forms for Aspheric Lenses
 - Available in a Variety of Sizes
 - [TECHSPEC® N-BK7 Half-Ball Lenses](#) Also Available
- TECHSPEC® N-BK7 Ball Lenses are glass spheres commonly used in fiber optic applications. Ball lenses are excellent optical components for improving signal coupling between fibers, emitters, and detectors. They are also used in endoscopy, bar code scanning, ball pre-forms for aspheric lenses, and sensor applications. TECHSPEC® N-BK7 Ball Lenses are uncoated and are optimal for wavelengths 350-2200nm. If applications require a more compact design, [TECHSPEC® N-BK7 Half-Ball Lenses](#) are also available.

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts