

[See all 25 Products in Family](#)

TECHSPEC® 8.5mm f/1.4, 75mm-∞ Primary WD, HRi Series Fixed Focal Length Lens



8.5mm f/1.4, 2/3" HPI Series Fixed Focal Length Lens, #37-746



Stock #36-746 **15 In Stock**

⊖ 1 ⊕ €625⁰⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1+ | €625,00 each |
| Need More? | Request Quote |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

HRi Series **Product Family:**

Fixed Focal Length Lens **Type:**

High Performance Lens with Fixed Apertures and Compact Form Factor **Imaging Lens Type:**

Physical & Mechanical Properties

| | |
|-------|--------------------------------------|
| Fixed | Iris Option: |
| 44.57 | Length (mm): |
| 40 | Maximum Diameter (mm): |
| 40 | Outer Diameter (mm): |
| 84 | Weight (g): |
| 1.31 | Maximum Rear Protrusion (mm): |

Optical Properties

Horizontal Field of View @ Max Sensor Format:
101.4mm - 56.8°

Field of View at Max Sensor Format:
Horizontal: 101.4mm - 56.8°
Vertical: 74.2mm - 43.5°
Diagonal: 130.5mm - 68.9°

Horizontal Field of View, 2/3" Sensor:
101.4mm - 56.8°

Horizontal Field of View, 1/1.8" Sensor:
81.5mm - 47.2°

Horizontal Field of View, 1/2" Sensor:
71.9mm - 42.2°

Horizontal Field of View, 1/2.5" Sensor:
64.8mm - 38.4°

Horizontal Field of View, 1/3" Sensor:
53.2mm - 32.0°

Horizontal Field of View, 1/4" Sensor:
39.6mm - 24.1°

Maximum Image Circle (mm):
11.00

Numerical Aperture NA, Object Side:
0.032

Number of Elements (Groups):
9 (8)

Focal Length FL (mm):
8.50

Working Distance (mm):
75 - ∞

Aperture (f/#):
f/1.4

Coating:
425 - 675nm BBAR

Coating Specification:
425 - 675nm BBAR

Entrance Pupil Position (mm):
18.85

Object Space Principal Plane (mm):
25.03

Image Space Principal Plane (mm):
4.70

Maximum Distortion (%):
-5.6

Exit Pupil Position (mm):
-17.93

Optimized Working Distance (mm):
75 - ∞

Lens Wavelength Range:
VIS

Sensor

Maximum Sensor Format:
2/3"

Pixel Size (µm):
1.85

Threading & Mounting

Filter Thread:
M58 x 0.75 (Male)

Filter Thread Adapter:

Front Thread:
M40 x 0.5 (Male)

Mount:
C-Mount

Environmental & Durability Factors

Storage Temperature (°C):
-20 to +60

Type of Ruggedization:
Industrial (Fixed Aperture with Simplified Mechanics)

Regulatory Compliance

Certificate of Conformance:
[View](#)

Product Details


- 2/3", C-Mount Lens
- Up to 10 MegaPixels, 1.85µm Pixel Size Sensors
- Instrumentation (HRi) Versions of our HR Series Lenses with Streamlined Mechanical Designs and Fixed Apertures
- 8.5mm to 12mm Focal Length
- **Ruggedized (HRr) Designs** Also Available

TECHSPEC® HRi Series Fixed Focal Length Lenses are a streamlined version of our HR Series Lenses. There are multiple options available for each focal length to accommodate a variety of optimized working distance ranges. Designed for high volume imaging applications, HRi series lenses feature simplified focus mechanics and a fixed aperture. TECHSPEC HRi Series Fixed Focal Length Lenses are available in a variety of f/# options, making them ideal for applications that require reduced size, cost, and lockable focus imaging solutions. Call for OEM Quantity Pricing.


Edmund Optics has created a family of high performance optical designs (the HR Series family) and developed three customized optomechanical solutions targeted for specific applications. These lens sub-families utilize the same optics as the HR Series Lenses, providing the same optical performance in a variety of optomechanical solutions to meet your application requirements:

- **HR Series:** Features locking cam focus and iris adjustment. This is the most adjustable version of these optical designs and is the typical high quality machine vision lens.
- **HRi Series:** Simplified mechanics featuring fixed apertures with compact housing. **Industrial Ruggedization** for reduced size, cost, and locked focus.
- **HRr Series:** All optics glued in place and a locking C-clamp focus ring. **Stabilized Ruggedization** for reduced pixel shift and improved focus stability.


Technical Information




#36-746, 8.5mm f/1.4, 75mm-∞ Primary WD, HRi Series Fixed Focal Length Lens, Distortion Plot



#36-746, 8.5mm f/1.4, 75mm-∞ Primary WD, HRi Series Fixed Focal Length Lens, Relative Illumination Plot




#36-746, 8.5mm f/1.4, 75mm-∞ Primary WD, HRi Series Fixed Focal Length Lens, Working Distance versus Field of View Plot




#36-746, 8.5mm f/1.4, 75mm-∞ Primary WD, HRi Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 200mm Working Distance, f1.4



#36-746, 8.5mm f/1.4, 75mm-∞ Primary WD, HRi Series Fixed Focal Length Lens, Depth of Field Plot, 200mm Working Distance, f1.4



#36-746, 8.5mm f/1.4, 75mm-∞ Primary WD, HRi Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 500mm Working Distance, f1.4



#36-746, 8.5mm f/1.4, 75mm-∞ Primary WD, HRi Series Fixed Focal Length Lens, Depth of Field Plot, 500mm Working Distance, f1.4

Compatible Cameras