

[See all 22 Products in Family](#)

## 9 - 40mm FL, CS-Mount, P-Iris, Wide Angle Lens



Image represents #22-793: Design will vary by stock number.

Stock **#22-798** **1 In Stock**

⊖ 1 ⊕ €422.<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	€422,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Product Family:  
Low Distortion Wide Angle Lenses

Type:  
Varifocal Lens

### Physical & Mechanical Properties

Iris Option:  
P-iris (Motorized)

Length (mm):

49.00	<b>Maximum Diameter (mm):</b>
55	
	<b>Outer Diameter (mm):</b>
55	
	<b>Weight (g):</b>
68	

## Optical Properties

	<b>Horizontal Field of View @ Max Sensor Format:</b>
39-9.2°	
	<b>Horizontal Field of View, 1/3" Sensor:</b>
30 - 7.1°	
	<b>Maximum Image Circle (mm):</b>
7.70	
	<b>Focal Length FL (mm):</b>
9.00	
	<b>Working Distance (mm):</b>
300 - ∞	
	<b>Aperture (f#):</b>
f/1.5 - Closed	
	<b>Lens Wavelength Range:</b>
VS	

## Sensor

	<b>Maximum Sensor Format:</b>
1/2.3"	
	<b>Pixel Size (µm):</b>
4.50	

## Threading & Mounting

	<b>Filter Thread:</b>
N/A	
	<b>Mount:</b>
CS-Mount	

## Regulatory Compliance

	<b>Certificate of Conformance:</b>
<a href="#">View</a>	

## Product Details

- Up to 1/2.5", C-Mount and CS-Mount options
- Up to 3 MegaPixel and Down to 1% Distortion
- No Refocusing from 100mm to Infinity
- 1.28mm to 40mm Focal Length

Low Distortion Wide Angle Lenses maintain high resolution for applications with long working distance requirements and can accommodate multi-megapixel camera sensors. The optical design of these low-distortion wide-angle lenses enables users to achieve less than 3% distortion over a 125° field of view, or less than 1% distortion over a 110° field of view. These lenses feature a locking screw for the manual iris enabling the use in high vibration environments. Low Distortion Wide Angle Lenses are ideal for security and surveillance, machine vision, or [factory automation](#) applications. These lenses do not require refocusing from 100mm to Infinity.

**Note:** Image will be flipped (180° rotation). Auto Iris Options require cameras with P-Iris or DC Iris control.