

TECHSPEC® 950nm CWL, 25mm Dia. Hard Coated OD 4.0 25nm Bandpass Filter



Stock #86-663 3-4 DAYS

[Additional Bandwidths](#)

⊖ 1 ⊕ **€261,00**

ADD TO CART

Qty 1-5

€261,00

Qty 6+

€205,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.1

Angle of Incidence (°):
0

Bandwidth (nm):

20

Optical Density OD (Average):

≥4.0

Clear Aperture CA (mm):

21.0

Center Wavelength CWL (nm):

950.00 ±3

Center Wavelength CWL Tolerance (nm):

±3

Full Width-Half Max FWHM (nm):

25.00 ±3

Full Width-Half Max FWHM Tolerance (nm):

±3

Substrate:

Optical Glass

Minimum Transmission (%):

≥90

Coating:

Hard Coated

Surface Quality:

80-50

Type:

Bandpass Filter

Blocking Wavelength Range (nm):

200 - 1200

Construction:

Mounted in Black Anodized Ring

Environmental Durability:Humidity per ML-STD-810H, Section 507.6
Temperature per ML-STD-810H, Section 501.7 and 502.7**Physical Durability:**Adhesion per ML-PRF-13830B, Section C.4.5.12
Moderate abrasion per ML-PRF-13830B, Section C.4.5.11
Cleaning per ML-C-48497A Section 4.5.4.2**Mount Thickness (mm):**

5.0 ±0.1

Substrate Thickness (mm):

3.5 ±0.5

Regulatory Compliance

RoHS 2015:[Compliant](#)**Reach 219:**[Compliant](#)**Certificate of Conformance:**[View](#)