

[See all 293 Products in Family](#)

TECHSPEC<sup>®</sup> 9mm Dia. x 40mm FL, VIS 0°, Inked, Achromatic Lens



Stock **#47-656-INK** [CONTACT US](#)

☐ [Other Coating Options](#)

-

1

+

€91<sup>.50</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | €91,50 each                   |
| Qty 6-25       | €73,50 each                   |
| Qty 26-49      | €69,00 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Achromatic Lens

Type:

Physical & Mechanical Properties

|                      |                             |
|----------------------|-----------------------------|
| 9.00 ±0.025          | Diameter (mm):              |
| 8.1                  | Clear Aperture CA (mm):     |
| <1                   | Centering (arcmin):         |
| 5.06 ±0.10           | Center Thickness CT (mm):   |
| 3.73 ±0.05           | Center Thickness CT 1 (mm): |
| 1.33 ±0.05           | Center Thickness CT 2 (mm): |
| 4.45                 | Edge Thickness ET (mm):     |
| Protective as needed | Bevel:                      |

|                                      |                                             |
|--------------------------------------|---------------------------------------------|
| Optical Properties                   |                                             |
| 40.00                                | Effective Focal Length EFL (mm):            |
| ±1                                   | Focal Length Tolerance (%):                 |
| 37.54                                | Back Focal Length BFL (mm):                 |
| 587.6                                | Focal Length Specification Wavelength (nm): |
| 24.77                                | Radius R <sub>1</sub> (mm):                 |
| -18.01                               | Radius R <sub>2</sub> (mm):                 |
| -51.17                               | Radius R <sub>3</sub> (mm):                 |
| N-BK7 / N-SF5                        | Substrate: <input type="text"/>             |
| 40-20                                | Surface Quality:                            |
| 4.44                                 | f/#:                                        |
| 0.11                                 | Numerical Aperture NA:                      |
| VIS 0° (425-675nm)                   | Coating:                                    |
| R <sub>avg</sub> ≤0.4% @ 425 - 675nm | Coating Specification:                      |
| 1.5λ                                 | Power (P-V) @ 632.8nm:                      |
| λ/4                                  | Irregularity (P-V) @ 632.8nm:               |
| 425 - 675                            | Wavelength Range (nm):                      |

|                       |                             |
|-----------------------|-----------------------------|
| Regulatory Compliance |                             |
| Compliant             | RoHS 2015:                  |
| Compliant             | Reach 209:                  |
| View                  | Certificate of Conformance: |

## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Designed for 0° Angle of Incidence
  - Less Than 0.4% Reflectance Per Surface from 425 - 675nm
  - [MgF<sub>2</sub>](#) and [VIS-NIR](#) Coated Achromats Also Available
- TECHSPEC® VIS 0° Coated Achromatic Lenses consist of two optical components cemented together to form an achromatic doublet. The doublet is computer optimized to correct for on-axis spherical and chromatic aberrations. Achromatic lenses are best for applications involving multi-color (white light) imaging due to their specific doublet lens pairing that enables them to correct the color separation inherent in glass. TECHSPEC® VIS 0° Coated Achromatic Lenses provide optimized transmission for 425 – 675nm, reducing average reflection to 0.4%. [MgF<sub>2</sub>](#) and [VIS-NIR](#) Coated Achromats are also available on our website.

Technical Information



Coating Curves

Compatible Mounts