

TECHSPEC<sup>®</sup> 9.0mm Diameter x -18 FL, NIR I, Inked, Plano-Concave Lens



Stock **#49-523-INK** [CONTACT US](#)  
☐ [Other Coating Options](#)

-

1

+

€57<sup>.00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | €57,00 each                   |
| Qty 10-25      | €51,00 each                   |
| Qty 26-49      | €45,75 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Plano-Concave Lens

Type:

Physical & Mechanical Properties


|                                       |                                                       |
|---------------------------------------|-------------------------------------------------------|
| 9.00 ±0.025                           | Diameter (mm):                                        |
| Protective as needed                  | Bevel:                                                |
| 2.25                                  | Center Thickness CT (mm):                             |
| ±0.05                                 | Center Thickness Tolerance (mm):                      |
| <1                                    | Centering (arcmin):                                   |
| 8.1                                   | Clear Aperture CA (mm):                               |
| 2.89                                  | Edge Thickness ET (mm):                               |
| Optical Properties                    |                                                       |
| -18.00                                | Effective Focal Length EFL (mm):                      |
| N-SF11                                | Substrate: <input type="checkbox"/>                   |
| 2.00                                  | f/#:                                                  |
| 0.25                                  | Numerical Aperture NA:                                |
| NIR I (600-1050nm)                    | Coating:                                              |
| 600 - 1050                            | Wavelength Range (nm):                                |
| -19.26                                | Back Focal Length BFL (mm):                           |
| R <sub>avg</sub> ≤0.5% @ 600 - 1050nm | Coating Specification:                                |
| 587.6                                 | Focal Length Specification Wavelength (nm):           |
| ±1                                    | Focal Length Tolerance (%):                           |
| -14.12                                | Radius R <sub>1</sub> (mm):                           |
| 40-20                                 | Surface Quality:                                      |
| 7 J/cm² @ 1064nm, 10ns                | Damage Threshold, By Design: <input type="checkbox"/> |
| 1.5λ                                  | Power (P-V) @ 632.8nm:                                |
| λ/4                                   | Irregularity (P-V) @ 632.8nm:                         |
| Regulatory Compliance                 |                                                       |
| View                                  | Certificate of Conformance:                           |

## Product Details

- AR Coated to Provide <0.5% Reflectance per Surface for 600 - 1050nm
- Designed for 0° Angle of Incidence
- Various Coating Options: [Uncoated](#), [VIS-EXT](#), [MgF<sub>2</sub>](#), [VIS 0°](#), [VIS-NIR](#), [YAG-BBAR](#), and [NIR II](#)


TECHSPEC® NIR I Coated Plano-Concave (PCV) Lenses are designed to bend parallel input rays to diverge from one another on the output side of the lens causing this lens to have a negative focal length. These lenses can be used for balancing aberrations created by other lenses within a system due to their negative spherical aberration. Plano-Concave (PCV) lenses are commonly used in a variety of applications including image reduction, beam expansion and telescopes. TECHSPEC® NIR I Coated Plano-Concave (PCV) Lenses offer optimal performance in the 600nm to 1050nm range. These lenses are also available [Uncoated](#), [VIS-EXT](#), [MgF<sub>2</sub>](#), [VIS 0°](#), [VIS-NIR](#), [YAG-BBAR](#), or with [NIR II](#) AR coating options.

## Technical Information




N-BK7

Uncoated N-BK7 Typical Transmission




Typical transmission of a 3mm thick, uncoated N-BK7 window across the UV- NIR spectra.  
[Click Here to Download Data](#)

N-BK7 with MgF<sub>2</sub> Coating  
Typical Transmission




Typical transmission of a 3mm thick N-BK7 window with MgF<sub>2</sub> (400-700nm) coating at 0° AOI.  
The blue shaded region indicates the coating design wavelength range, with the following specification:  
 $R_{avg} \leq 1.75\% @ 400 - 700\text{nm}$  (N-BK7)  
Data outside this range is not guaranteed and is for reference only.  
[Click Here to Download Data](#)

N-BK7 with VIS-EXT Coating  
Typical Transmission








Typical transmission of a 3mm thick N-BK7 window with VIS-EXT (350-700nm) coating at 0° AOI.  
The blue shaded region indicates the coating design wavelength range, with the following specification:  
 $R_{avg} \leq 0.5\% @ 350 - 700\text{nm}$   
Data outside this range is not guaranteed and is for reference only.  
[Click Here to Download Data](#)

N-BK7 with VIS-NIR Coating  
Typical Transmission



Typical transmission of a 3mm thick N-BK7 window with VIS-NIR (400-1000nm) coating at 0° AOI.  
The blue shaded region indicates the coating design wavelength range, with the following specification:  
 $R_{abs} \leq 0.25\% @ 880\text{nm}$   
 $R_{avg} \leq 1.25\% @ 400 - 870\text{nm}$   
 $R_{avg} \leq 1.25\% @ 890 - 1000\text{nm}$   
Data outside this range is not guaranteed and is for reference only.  
[Click Here to Download Data](#)

|                                                                                                                                                                                             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|                                                                                                            |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
| <p data-bbox="596 261 974 350"><b>N-BK7 with VIS 0° Coating</b><br/><b>Typical Transmission</b></p>       | <p data-bbox="1339 394 1843 442">Typical transmission of a 3mm thick N-BK7 window with VIS 0° (425-675nm) coating at 0° AOI.</p> <p data-bbox="1339 457 1850 504">The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p data-bbox="1478 519 1711 543"><math>R_{avg} \leq 0.4\% @ 425 - 675\text{nm}</math></p> <p data-bbox="1339 557 1839 605">Data outside this range is not guaranteed and is for reference only.</p> <p data-bbox="1474 620 1711 644"><a href="#">Click Here to Download Data</a></p>                                                                                                                                                                                                        |
| <p data-bbox="569 857 1037 946"><b>N-BK7 with YAG-BBAR Coating</b><br/><b>Typical Transmission</b></p>   | <p data-bbox="1339 985 1839 1032">Typical transmission of a 3mm thick N-BK7 window with YAG-BBAR (500-1100nm) coating at 0° AOI.</p> <p data-bbox="1339 1047 1850 1095">The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p data-bbox="1493 1110 1688 1133"><math>R_{abs} \leq 0.25\% @ 532\text{nm}</math></p> <p data-bbox="1493 1136 1692 1160"><math>R_{abs} \leq 0.25\% @ 1064\text{nm}</math></p> <p data-bbox="1472 1163 1713 1187"><math>R_{avg} \leq 1.0\% @ 500 - 1100\text{nm}</math></p> <p data-bbox="1339 1202 1839 1249">Data outside this range is not guaranteed and is for reference only.</p> <p data-bbox="1474 1264 1711 1288"><a href="#">Click Here to Download Data</a></p>            |
| <p data-bbox="617 1495 1008 1584"><b>N-BK7 with NIR I Coating</b><br/><b>Typical Transmission</b></p>   | <p data-bbox="1339 1647 1839 1694">Typical transmission of a 3mm thick N-BK7 window with NIR I (600 - 1050nm) coating at 0° AOI.</p> <p data-bbox="1339 1709 1850 1757">The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p data-bbox="1472 1771 1713 1795"><math>R_{avg} \leq 0.5\% @ 600 - 1050\text{nm}</math></p> <p data-bbox="1339 1810 1839 1857">Data outside this range is not guaranteed and is for reference only.</p> <p data-bbox="1474 1872 1711 1896"><a href="#">Click Here to Download Data</a></p>                                                                                                                                                                                           |
| <p data-bbox="606 2133 1016 2223"><b>N-BK7 with NIR II Coating</b><br/><b>Typical Transmission</b></p>  | <p data-bbox="1339 2255 1843 2303">Typical transmission of a 3mm thick N-BK7 window with NIR II (750 - 1550nm) coating at 0° AOI.</p> <p data-bbox="1339 2318 1850 2365">The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p data-bbox="1474 2380 1711 2404"><math>R_{abs} \leq 1.5\% @ 750 - 800\text{nm}</math></p> <p data-bbox="1474 2407 1711 2430"><math>R_{abs} \leq 1.0\% @ 800 - 1550\text{nm}</math></p> <p data-bbox="1472 2433 1713 2457"><math>R_{avg} \leq 0.7\% @ 750 - 1550\text{nm}</math></p> <p data-bbox="1339 2472 1839 2519">Data outside this range is not guaranteed and is for reference only.</p> <p data-bbox="1474 2534 1711 2558"><a href="#">Click Here to Download Data</a></p> |

# Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Compatible Mounts

;