

TECHSPEC® 9mm Dia. x 9mm FL Uncoated, Double-Convex Lens



Stock **#32-018** ☐ In Stock
[Other Coating Options](#)

1 **€29,50**

ADD TO CART

Qty 1-9
€29,50
Qty 10+
€26,50
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
9.00 +0.0/-0.025

Back Focal Length BFL (mm):

7.90
Effective Focal Length EFL (mm): 9.00
Coating: Uncoated
Substrate: 
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <3
Bevel: Protective bevel as needed
Center Thickness CT (mm): 3.45
Center Thickness Tolerance (mm): ±0.05
Edge Thickness ET (mm): 1.60
Radius R ₁ =R ₂ (mm): 11.38
Clear Aperture CA (mm): 8.1
f/#: 1.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.50
Type: Double-Convex Lens
Wavelength Range (nm): 380 - 2500

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant