


a-BBO Rochon Polarizer



Stock #68-827 **20+ In Stock**

⊖ 1 ⊕ €1.275⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	€1.275,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Linear Polarizer **Type:**

Physical & Mechanical Properties

10.0 **Clear Aperture CA (mm):**

25.40 **Diameter (mm):**

18.00 **Length (mm):**

Dimensional Tolerance (mm):
+0.0/-0.2

Construction:
Crystalline Rochon Polarizer

Length Tolerance (mm):
±0.1

Housing:
Black Anodized Aluminum

Optical Properties

Extinction Ratio:
200,000:1

Substrate: □
α-BBO

Surface Quality:
20-10

Transmitted Wavefront, P-V:
λ/4 @ 632.8nm

Beam Deviation (arcmin):
<3

Wavelength Range (nm):
200 - 3500

Damage Threshold, By Design: □
10 J/cm² @ 1064nm, 20ns

Separation Angle (°):
8.0 - 14 (8 @ 800nm)

Regulatory Compliance

Certificate of Conformance:
[View](#)


Product Details

- Multiple Polarization Materials Available
- Ordinary Rays Pass Through Undeviated
- Extraordinary Rays Deviate
- [Wollaston Polarizers](#) Also Available


Rochon Polarizers consist of two birefringent material prisms in optical contact with one another. The ordinary and extraordinary rays remain collinear through the first prism. Upon entering the second prism, the ordinary rays do not experience a change in the refractive index and pass through the prism without deviation, while the extraordinary rays refract at the interface.

LASER OPTICS MADE BY EDMUND OPTICS® [LEARN MORE](#)

Technical Information



Stock No.	Outer Diameter	Clear Aperture	Length
#68-824	25.4mm	10.0mm	28.0mm
#68-825	25.4mm	10.0mm	28.0mm
#68-826	25.4mm	10.0mm	16.0mm
#68-827	25.4mm	10.0mm	18.0mm



;