

TECHSPEC® 9mm Dia. x 27mm FL, MgF₂ Coated, Achromatic Doublet Lens



MgF₂ Coated Achromatic Lenses



Stock **#45-092** [CONTACT US](#)

[Other Coating Options](#)

⊖ 1 ⊕

€67,00

ADD TO CART

Qty 1-5

€67,00

Qty 6+

€53,50

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
9.00 +0.0/-0.025

Effective Focal Length EFL (mm): 27.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 24.22
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 8.1
Centering (arcmin): <1
Center Thickness CT (mm): 5.19 ±0.10
Center Thickness CT 1 (mm): 3.89 ±0.05
Center Thickness CT 2 (mm): 1.30 ±0.05
Radius R₁ (mm): 15.36
Radius R₂ (mm): -12.01
Radius R₃ (mm): -39.56
Edge Thickness ET (mm): 4.26
Substrate: N-BK7 / N-SF5
Surface Quality: 40-20
f/#: 3.00
Numerical Aperture NA: 0.17
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View