

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 9mm Dia. X -9mm FL, NIR II Coated, Double-Concave Lens



Stock #68-008 ☐ In Stock
[Other Coating Options](#)

-

1

+

 €39,50

ADD TO CART

Qty 1-9
€39,50

Qty 10+
€35,50

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
9.00 +0.0/-0.025

Effective Focal Length EFL (mm):

-9.00
Substrate: N-SF11
f#: 1.00
Numerical Aperture NA: 0.50
Coating: NIR II (750-1550nm)
Type: Double-Concave Lens
Wavelength Range (nm): 750 - 1550
Back Focal Length BFL (mm): -9.61
Center Thickness CT (mm): 2.25
Center Thickness Tolerance (mm): ±0.05
Centering (arcmin): <3
Clear Aperture CA (mm): 8.10
Coating Specification: R_{abs} ≤1.5% @ 750 - 800nm R_{abs} ≤1.0% @ 800 - 1550nm R_{avg} ≤0.7% @ 750 - 1550nm
Edge Thickness ET (mm): 3.48
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1.00
Radius R₁=R₂ (mm): -14.60
Surface Quality: 40-20
Damage Threshold, By Design: 8 J/cm² @ 1064nm, 10ns
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View