


DoAll Light



Stock #75-233 **NEW** [CONTACT US](#)

⊖ 1 ⊕ €7.350⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	€7.350,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

DoAll-UR-PS-Kit **Model Number:**

LED Illuminator **Type of Illumination:**

Smart Vision Lights LLC **Manufacturer:**

Geometry:

Dome Light, Low Angle Darkfield Ringlight, Mid Angle Darkfield Ringlight, RGBW Ringlight, Four Quadrant Ringlight, NIR Ringlight

Illumination Mode:

Constant or Strobed

Physical & Mechanical Properties

Dimensions (mm):

213.44 Dia. x 112.88 H

Weight (kg):

1.58

Optical Properties

Color:

RGB-IR

Working Distance (mm):

0 - 750

Electrical

Output Current (A):

15 A for both outputs combined

Hardware & Interface Connectivity

Connector:

2 5-Pin M12 Connectors

Regulatory Compliance

Certificate of Conformance:

[View](#)

Product Details

- All-In-One Solution for Machine Vision Lighting Applications
- Combines 6 Illumination Geometries into One Multi-Functional Illuminator
- Features RGB, White and NIR Illumination

The Smart Vision Lights DoAll Light provides an all-in-one solution for machine vision lighting applications that require various wavelengths and illumination profiles. This light combines a dome, low and mid angle darkfield ring, RGBW ring, four-quadrant ring, and NIR ring light into one system. The included controller allows the user to program and save multiple illumination sequence variations for ease of use between inspections. The Smart Vision DoAll Light features RGB, white, and NIR illumination to address multiple application spaces. This versatile illuminator includes all required components for operation, including the controller, power supply, power & ethernet cables, URCap USB stick with software, and mounting hardware. The DoAll Light's compact size allows for easy integration into smaller electronic assembly inspection systems or for use in large-scale automatic and logistics applications.

Color	Dominant Wavelength	Irradiance	OverDrive™ Irradiance	Illuminance	OverDrive™ Illuminance
Red	625 nm	1.4 mW/cm ²	10.6 mW/cm ²	2,469 lux	18,300 lux
Green	533 nm	1.9 mW/cm ²	9.5 mW/cm ²	10,420 lux	51,900 lux
Blue	484 nm	2.5 mW/cm ²	14.1 mW/cm ²	2,860 lux	15,900 lux
White	556 (5443 K)	2.8 mW/cm ²	17.6 mW/cm ²	8,960 lux	57,100 lux
IR	850 nm	8.2 mW/cm ²	36.6 mW/cm ²	N/A	N/A