

## Dual Axis Linear Scale Micrometer



Stock #58-608 **4 In Stock**

€665<sup>.00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-4	€665,00 each
Qty 5+	€632,30 each
Need More?	<a href="#">Request Quote</a>

**i** Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

No **NST Certification:**

### Physical & Mechanical Properties

Metric: 25µm  
English: 1 mil (0.001") **Scale Divisions:**

25.4 x 76.2 **Dimensions (mm):**

1.50 ±0.100      **Thickness (mm):**

±0.100      **Dimensional Tolerance (mm):**

## Optical Properties

Chrome on Glass      **Substrate:**

60-40      **Surface Quality:**

## Regulatory Compliance

[Compliant](#)      **RoHS 2015:**

[View](#)      **Certificate of Conformance:**

[Compliant](#)      **Reach 235:**

## Product Details

- Dual Axis Design
- English and Metric Scales
- NIST Certified Version Available

Our Linear Scale Stage Micrometer is designed to accurately calibrate machine vision systems simultaneously in the X- and Y- axes. This allows calibration without rotation, and without compensation for camera aspect ratios. Micrometer features two scales – a metric scale featuring 25µm divisions, and an English scale featuring 1 mil (0.001") divisions. Target is chrome on glass or chrome on opal.

## Technical Information

