

[See all 36 Products in Family](#)

Dual Bandpass Red-NIR Filter M25.5



Stock **#74-559** NEW **1 In Stock**

- 1 + €241^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	€241,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

Full Width-Half Max FWHM Range (nm):
40nm, 50nm ±5 nm

General

Type:

Dual Bandpass Mounted Imaging Filter

Model Number:

DB660/850-25.5

Physical & Mechanical Properties

Outer Diameter (mm):
27.5

2mm	Substrate Thickness (mm):
Optical Properties	
Red-NIR	Color:
40/20	Surface Quality:
≥90%	Transmission (%):
645-675nm, 830-870nm	Transmission Wavelength (nm):
Threading & Mounting	
M25.5 x 0.50	Filter Thread:
5.2	Mount Thickness (mm):
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Block and Transmit Desired Key VIS and NIR Spectral Bands with One Filter
- Remove The Need for Dual Sensor Setups
- Anti-Reflection Coating for Durability and Performance
- Various Mounting Thread Options Available

Multi-Band Machine Vision Bandpass Filters feature both double or triple bandpass options in one filter, allowing for greater flexibility in system design. These filters are designed with up to ≥90% transmission in the visible (VIS) or near-infrared (NIR) spectra with various wavelength range combinations available. Additionally, these filters are AR coated for optimal transmission and feature a hard-coated, single-substrate design with superior surface quality to maximize optical performance. Multi-Band Machine Vision Bandpass Filters ensure accurate color reproduction by blocking unwanted wavelengths, eliminating the need for dual-sensor imaging. These filters are ideal for surveillance applications such as, security and intelligent traffic management, as well as normalized difference vegetation index (NDVI) imaging applications.

Note: Other filter threads are available upon request.