

[See all 36 Products in Family](#)

Astronomy Bandpass Filter, Kron-Cousins, Red 50 x 50mm



Astronomy Bandpass Filters

Stock **#21-118** [CONTACT US](#)

-

1

+

€890⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	€890,00 each
Qty 6-25	€801,00 each
Qty 26-49	€753,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type of Filter:

Kron-Cousins, R

Type:

Bandpass Filter

Physical & Mechanical Properties

Dimensions (mm):

50 x 50	
	Thickness (mm):
5.00 ±0.1	
	Dimensional Tolerance (mm):
+0/-0.25	
	Parallelism (arcsec):
<30	

Optical Properties	
	Center Wavelength CWL (nm):
630.00	
	Full Width-Half Max FWHM (nm):
250.00	
	Minimum Transmission (%):
>70	
	Surface Quality:
60-40	
	Transmitted Wavefront, RMS:
λ/4	

Regulatory Compliance	
	RoHS 2015:
Compliant	
	Certificate of Conformance:
View	
	REACH 241:
Compliant	

Product Details

- Filter and Measure Light from Astronomical Objects
- Ideal for Photometric Calibration
- UBVRI Filters

Astronomy Bandpass Filters are used to filter out and measure specific bands of light emitted by astronomical and celestial objects. Johnson/Bessel filters are well suited for use with photomultiplier tubes and Kron/Cousin filters are well suited for use with Silicon sensors because of the sensors' responsivity. Both types of filters utilize identical UV (U), Blue (B), and Violet (V) filters. However, the Red (R) and Infrared (I) filters are optimized for use with either a photomultiplier tube or silicon CCD detector. Astronomy Bandpass Filters have precisely controlled thicknesses to minimize the common problem of refocusing when changing filters.

Technical Information

