

Coherent® EnergyMax 1110746 | 500μJ-1000mJ, DB25

See More by [Coherent®](#)



Coherent® EnergyMax Laser Energy Sensors

Stock **#12-386** [CONTACT US](#)

-

1

+

€1.785⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€1.785,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Model Number:

J-25MB-HE
Coherent Part Number: 1110746

Type:

Meter required	
±3	Linearity (%):
±2	Calibration Uncertainty (%):
<16	Noise Equivalent Energy (μJ):
#35-203 or #66-277	Compatible Meters:
500mJ/cm² (10ns, 1064nm)	Maximum Incident Energy Density:
500μJ - 1J	Energy Range:
#88-412	Preferred Meter:
Physical & Mechanical Properties	
25	Active Area Diameter (mm):
Optical Properties	
1064	Calibration Wavelength (nm):
17	Maximum Pulse Width (μs):
190 - 12000	Wavelength Range (nm):
Sensor	
Pyroelectric	Type of Sensor:
Electrical	
1000	Maximum Repetition Rate (pps):
5	Maximum Incident Beam Power (W):
Hardware & Interface Connectivity	
DB25	Connector:
2.5	Length of Cable (m):
Regulatory Compliance	
Exempt	RoHS 2015:
Contains SVHC(s)	Reach 224:
View	Certificate of Conformance:

PRODUCT DETAILS

- ISO 17025 Certified
- Embedded Spectral Compensation Characteristics
- Automatic Temperature Compensation

Coherent® EnergyMax Laser Energy Sensors are designed for a variety of demanding laser measurement applications. These energy sensors, available in meter or meterless USB configurations, incorporate a diffuse coating to minimize specular reflection and feature large active areas. The J-50MB-YAG combines the MaxBlack coating with a diffuser for use with high energy lasers of up to 3J. Coherent® EnergyMax Laser Energy Sensors utilize onboard sensors to automate temperature compensation for improved measurement accuracy.