

Preloaded Norland Optical Adhesive NOA 86TLH Dispensing Barrel (10cc)

See More by [Norland](#)



10cc Dispensing Barrel for NOA (NOA60 shown as an example)

Stock **#14-796** [CONTACT US](#)

- 1 + **€38,00**

ADD TO CART

Qty 1-4
€38,00

Qty 5+
€35,70

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Size (oz):
0.34

Glass Bonding:
Excellent

Metal Bonding:
Excellent

Plastic Bonding: Excellent/Good
Viscosity (cps): 8000 - 10,000
Durability: Hard & Brittle
Index of Refraction n_d: 1.55 @ 589nm
Norland Number: 86TLH
Shelf Life: 4 months
Type: Barrel
Typical Applications: Higher viscosity optical adhesive meets Bellcore specification of 85C/85RH for bonding glass. Cured with UV, visible light and/or heat.
Note: Heat curing (-H suffix) adhesives are oxygen inhibited. If used on the surface of a substrate, the adhesive will need to be cured under an inert atmosphere (like nitrogen) to fully cure.
Absorption Range (nm): 314 - 420
Bonding Type: Glass to Glass/Metal
Energy for Full Cure (J/cm²): 2.5

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant