


Dual Axis Linear Scale Micrometer



Stock **#58-608** 1 In Stock

-

1

+

€665^{.00}

ADD TO CART

Volume Pricing	
Qty 1-4	€665,00 each
Qty 5+	€632,30 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
No	NIST Certification:
Physical & Mechanical Properties	
Metric: 25µm English: 1 mil (0.001")	Scale Divisions:
25.4 x 76.2	Dimensions (mm):

1.50 ±0.100	Thickness (mm):
±0.100	Dimensional Tolerance (mm):

Optical Properties	
Chrome on Glass	Substrate:
60-40	Surface Quality:

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

Product Details

- Dual Axis Design
 - English and Metric Scales
 - NIST Certified Version Available
- Our Linear Scale Stage Micrometer is designed to accurately calibrate machine vision systems simultaneously in the X- and Y- axes. This allows calibration without rotation, and without compensation for camera aspect ratios. Micrometer features two scales – a metric scale featuring 25µm divisions, and an English scale featuring 1 mil (0.001") divisions. Target is chrome on glass or chrome on opal.

Technical Information

