

Dual Bandpass Blue-NIR Filter M37



Stock **#74-542** NEW **1 In Stock**

-

1

+

€268^{,83}

ADD TO CART

Volume Pricing	
Qty 1+	€268,83 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Dual Bandpass Mounted Imaging Filter

Type:

DB475/850-37

Model Number:

Full Width-Half Max FWHM Range (nm):

45nm, 60nm ±5 nm	
Physical & Mechanical Properties	
39	Outer Diameter (mm):
1mm	Substrate Thickness (mm):
Optical Properties	
Blue-NIR	Color:
40/20	Surface Quality:
≥90%	Transmission (%):
460-490nm, 830-870nm	Transmission Wavelength (nm):
Threading & Mounting	
M37 x0.75	Filter Thread:
5.2	Mount Thickness (mm):
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- Block and Transmit Desired Key VIS and NIR Spectral Bands with One Filter
 - Remove The Need for Dual Sensor Setups
 - Anti-Reflection Coating for Durability and Performance
 - Various Mounting Thread Options Available
- Multi-Band Machine Vision Bandpass Filters feature both double or triple bandpass options in one filter, allowing for greater flexibility in system design. These filters are designed with up to ≥90% transmission in the visible (VIS) or near-infrared (NIR) spectra with various wavelength range combinations available. Additionally, these filters are AR coated for optimal transmission and feature a hard-coated, single-substrate design with superior surface quality to maximize optical performance. Multi-Band Machine Vision Bandpass Filters ensure accurate color reproduction by blocking unwanted wavelengths, eliminating the need for dual-sensor imaging. These filters are ideal for surveillance applications such as, security and intelligent traffic management, as well as normalized difference vegetation index (NDVI) imaging applications.
- Note:** Other filter threads are available upon request.