

[See all 33 Products in Family](#)

IDS U3-3274LE-C-HQ, USB 3.0, 1/1.8" Color Camera

See More by [IDS Imaging Development Systems](#)



IDS Imaging uEye LE/XLE Camera (C/CS - Mount, Board Level, Front View)



Stock **#24-122** **1 In Stock**

[Similar Cameras](#)

-

1

+

€505^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	€505,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

Color

Spectrum:

General

Color Camera

Type:

Model Number:

U3-3274LE-C-HQ	
IDS Imaging Development Systems	Manufacturer:
uEye+ LE	Camera Series:

Physical & Mechanical Properties

36 x 36 x 20 (excludes connectors and lens mount)	Dimensions (mm):
20	Weight (g):
Board Level	Housing:

Sensor

Not Specified	Image Buffer:
1/1.8"	Sensor Format:
3.10	Resolution (Megapixels):
58.00	Frame Rate (fps):
2,056 x 1,542	Pixels (H x V):
3.45 x 3.45	Pixel Size, H x V (µm):
7.093 x 5.32	Sensing Area, H x V (mm):
Sony IMX265	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Global	Shutter Type:
12 bit	Pixel Depth:
0.03ms - 1900ms	Exposure Time:
70.00	Dynamic Range (dB):
USB3 Vision	Machine Vision Standard:

Electrical

1 - 2	Power Consumption (W):
-------	------------------------

Hardware & Interface Connectivity

USB 3.0	Interface:
USB Type-C	Connector:
Power over USB	Power Supply:
2 Flash Output, 2 Trigger Input, 2 GPIO, 2 TWI, 1 Voltage Output, 1 Ground	GPIOs:
Hardware Trigger (GPIO); Software Trigger	Synchronization:
Back Panel (Right Angle)	Interface Port Orientation:
10-pin Wuerth connector (WR-WTB 1.00 mm)	GPIO Connector Type:

Threading & Mounting

C/CS-Mount	Mount:
N/A	Mounting Threads:

Environmental & Durability Factors

0 to +55	Operating Temperature (°C):
	Storage Temperature (°C):

Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	REACH 241:

Product Details

- Up to 8.0MP Resolution with Framerates up to 230fps
- Board Level Options with C/CS-Mount or S-Mount Available
- GenICam USB3 Vision Compliant

IDS Imaging uEye LE/XLE USB3.1 Cameras utilize [IDS Imaging's peak SDK platform](#) that supports GenICam and USB3 Vision standards for ease of software development and integration. These cameras are available in board-level or housed options with S-Mount or C/CS-Mount versions. The C/CS-Mount configurations come with a 5mm spacer to easily adapt between C-Mount and CS-Mount lenses. IDS Imaging uEye LE/XLE USB3.1 Cameras are ideal for small device construction, medical technology, robotics, and machine vision applications. With a compact design, the XLE version is suitable for integration into embedded systems whereas the LE version is suitable for small device projects.