

Coherent® LightSmyth™ 1500 - 1800nm, 711.24 Grooves/mm, 31.8 x 20mm Transmission Diffraction Grating

See More by [Coherent®](#)



LightSmyth™ Transmission Diffraction Gratings

Stock **#16-878** CLEARANCE CONTACT US

- 1 + **€874,95**

ADD TO CART

Qty 1+
€874,95

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Groove Density (grooves/mm):
711.24

Groove Density Uniformity (grooves/mm):
0.001

Wavelength Range (nm):
1500 - 1800

Minimum Efficiency (%): ≥95 @ 1500 - 1800nm
Dimensions (mm): 31.80 x 20.00
Angle of Incidence (°): 35.55 ±1
Clear Aperture CA (mm): 30.80 x 19.00
Coating: Dielectric
Construction: Multi-Layer Dielectric Binary Etch Grating
Length (mm): 31.80
Model Number: 1358003
Substrate:  Fused Silica (Corning 7980)
Surface Quality: 60-40
Thickness (mm): 0.95 ±0.050
Type: Transmission Diffraction Grating
Width (mm): 20.00
Alignment of Grooves to Edge (°): 0.1 (typical)
Polarization: S and P
Note: S-Polarization defined with E-field parallel to the grating grooves

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View