

TECHSPEC<sup>®</sup> Elliptical Mirror 31.75mm Minor Axis Enhanced Aluminum



Stock **#32-133** 11 In Stock

-

1

+

€133<sup>.00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | €133,00 each                  |
| Qty 6-25       | €106,00 each                  |
| Qty 26-49      | €100,00 each                  |
| Need More?     | <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Flatness specification is Peak to Valley

Note:

|                                          |                                                       |
|------------------------------------------|-------------------------------------------------------|
| Flat Mirror                              | Type:                                                 |
| Physical & Mechanical Properties         |                                                       |
| 31.75                                    | Minor Axis (mm):                                      |
| 44.91                                    | Major Axis (mm):                                      |
| ±0.38                                    | Dimensional Tolerance (mm):                           |
| ±0.015                                   | Dimensional Tolerance (inches):                       |
| 28.56 (Minor Axis)<br>40.41 (Major Axis) | Clear Aperture CA (mm):                               |
| 9.53 ±0.76                               | Thickness (mm):                                       |
| ±0.030                                   | Thickness Tolerance (inches):                         |
| Optical Properties                       |                                                       |
| λ/8                                      | Surface Flatness (P-V):                               |
| BOROFLOAT®                               | Substrate: <input type="checkbox"/>                   |
| 60-40                                    | Surface Quality:                                      |
| R <sub>avg</sub> >95% @ 450 - 650nm      | Coating Specification:                                |
| Enhanced Aluminum (450-650nm)            | Coating:                                              |
| Metal                                    | Coating Type:                                         |
| 0.45 - 0.65                              | Wavelength Range (μm):                                |
| 450 - 650                                | Wavelength Range (nm):                                |
| 0.2 J/cm <sup>2</sup> @ 532nm, 10ns      | Damage Threshold, Reference: <input type="checkbox"/> |
| Regulatory Compliance                    |                                                       |
| Compliant                                | RoHS 2015:                                            |
| View                                     | Certificate of Conformance:                           |
| Compliant                                | Reach 247:                                            |

## PRODUCT DETAILS

See Figure A in Technical Information tab for dimensional diagram.

- Circular Profile When Oriented at 45°
- Ideal for Redirecting Light
- Multiple Sizes and Coatings Offered

TECHSPEC® λ/8 Precision Elliptical Flat Mirrors are ideal for research and astronomical applications. Because of their elongated major axis, they are suited to bending and folding light at precise angles with minimum wavefront distortion. These mirrors have a circular profile when they are oriented at 45°. TECHSPEC® λ/8 Precision Elliptical Flat Mirrors feature a BOROFLOAT® substrate. Multiple sizes and coating options are offered to best suit a wide range of applications.

## TECHNICAL INFORMATION

| Fig. | Minor Axis (mm) | Major Axis (mm) | Thickness (mm) | Stock No. |                    |                      |                   |                |                  |
|------|-----------------|-----------------|----------------|-----------|--------------------|----------------------|-------------------|----------------|------------------|
|      |                 |                 |                | Uncoated  | Protected Aluminum | UV Enhanced Aluminum | Enhanced Aluminum | Protected Gold | Protected Silver |
| B    | 12.70           | 17.96           | 3.81           | #32-270   | #32-271            | #43-573              | #32-272           | #32-273        | #89-454          |
| B    | 22.23           | 31.42           | 6.35           | #32-093   | #30-836            | #43-574              | #32-131           | #32-085        | #89-455          |
| B    | 26.97           | 38.15           | 6.35           | #32-094   | #30-837            | #43-575              | #32-132           | #32-086        | #89-456          |
| A    | 31.75           | 44.91           | 9.53           | #32-095   | #30-205            | #43-576              | #32-133           | #32-087        | #89-457          |
| A    | 38.10           | 53.87           | 9.53           | #32-096   | #30-258            | #43-577              | #32-134           | #32-088        | #89-458          |

