

TECHSPEC® f/1.9, 6mm Focal Length Green Series M12 Lens



6mm Focal Length

Stock **#87-231** 3-4 DAYS

⊖ 1 ⊕ **€87,00**

ADD TO CART

Qty 1-49

€87,00

Qty 50+

€69,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length (mm):
11.70

Maximum Diameter (mm):
14

Outer Diameter (mm):
14.00

Resolution: 80 lp/mm @ 20% Contrast
Mounting Threads: M12 x0.5
Weight (g): 3
Horizontal Field of View, 1/3" Sensor: 129.8mm - 46.2°
Maximum Image Circle (mm): 6.00
Numerical Aperture NA, Object Side: 0.0100
Horizontal Field of View @ Max Sensor Format: 129.8mm - 46.2°
Number of Elements (Groups): 5(5)
Wavelength Range (nm): 400 - 700
Type: M12 Imaging Lens
Focal Length FL (mm): 6.00
Primary Magnification PMAG: 0.039X
Maximum Sensor Format: 1/3"
Working Distance (mm): 150 - ∞
Mount: M12 x0.5 (S-Mount)
Aperture (f/#): f/1.9
Distortion (%): -8.27 @ Full Field
Back Focal Length BFL (mm): 4.0 - 3.9
Coating Specification: λ/4 MgF ₂ @ 580nm
Entrance Pupil Position (mm): 3.99
Horizontal Field of View, 1/4" Sensor: 95.1mm - 34.7°
Object Space Principal Plane (mm): 6.38
Image Space Principal Plane (mm): -1.43
Field of View at Max Sensor Format: Horizontal: 129.8mm - 46° Vertical: 95.2mm - 34.6° Diagonal: 168.5mm - 57.7°
IR Cut Filter: No
Exit Pupil Position (mm): -5.43
Lens Wavelength Range: VIS
Imaging Lens Type: Standard Lens

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant