

JAI Apex, 1600T-PGE, 1/2.9" 1.6MP, GigE Color Camera



Stock #29-163 1 In Stock

-

1

+

€3.010⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€3.010,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

Color	Spectrum:
General	
Color Camera	Type:
AP-1600T-PGE-1	Model Number:
JAI	Manufacturer:
	Camera Series:

Apex	
Physical & Mechanical Properties	
44 x 44 x 74	Dimensions (mm):
170	Weight (g):
Full	Housing:
Sensor	
1/2.9"	Sensor Format:
1.60	Resolution (Megapixels):
24.00	Frame Rate (fps):
1,456 x 1,088	Pixels (H x V):
3.45 x 3.45	Pixel Size, H x V (µm):
4.97 x 3.73	Sensing Area, H x V (mm):
Sony IMX273	Imaging Sensor:
3 Color RGB CMOS	Type of Sensor:
Global	Shutter Type:
12 bit	Pixel Depth:
GigE Vision	Machine Vision Standard:
Electrical	
5.3	Power Consumption (W):
Hardware & Interface Connectivity	
GigE (PoE)	Interface:
RJ45 with Screw Locks	Connector:
Power Supply Required and Sold Separately. USA: #29-172 Europe: #29-172 Japan: #29-172 Korea: Not Available China: Not Available	Power Supply:
Hardware Trigger (GPIO) or Software Trigger	Synchronization:
Back Panel	Interface Port Orientation:
12-pin Hirose	GPIO Connector Type:
Threading & Mounting	
C-Mount	Mount:
Environmental & Durability Factors	
-5 to +45	Operating Temperature (°C):
-25 to +60	Storage Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- High Color Fidelity and Spatial Precision versus Bayer Color Cameras
- More Accurate Per-Pixel Color Values, Steeper Spectral Curves, Sharper Resolution
- USB, GigE, and Medical Versions Available

JAI® APEX Series 3-Sensor Cameras are a range of 3-CMOS area scan cameras that provide better color fidelity and spatial precision than traditional Bayer color cameras. Utilizing a prism at the camera input, the incoming light is separated into red, green, and blue wavelengths which are each directed to separate red, green, and blue image sensors. These sensors deliver true red, green, and blue color outputs for more accurate per-pixel color values, steeper spectral curves, and sharper resolution. JAI® APEX Series 3-Sensor Cameras are available in 1.6 or 3.2 megapixel resolutions with USB or Gigabit Ethernet (GigE) outputs, and also available in a white housing with USB output that offers strict production screening and preventative measures to minimize dust, lint, or debris on the prism, sensor, or in the optical path for clinical environments and life science applications. These cameras are ideal for a range of medical and laboratory applications such as fluorescence microscopy, digital pathology, ophthalmology, endoscopy, surgical imaging, and medical quality inspection.