

TECHSPEC® Finite Conjugate, DUV Coated, 15X/0.28NA HP ReflX



High Performance ReflX™ Objectives

Stock #59-885 3-4 DAYS

- 1 + **€2.459,00**

ADD TO CART

Qty 1+

€2.459,00

Qty 2+

€2.170,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Entrance Pupil Position (mm):
40.0

Field of View (mm):
150

Horizontal Field of View, 1/2" Sensor:
0.43mm

Horizontal Field of View, 2/3" Sensor: 0.59mm
Focal Length FL (mm): 12.97
Coating: DUV Enhanced Aluminum (150-11000nm)
Magnification: 15X
Mount: RMS
Numerical Aperture NA: 0.28
Type: Microscope Objective
Obscuration (%): 27.00
Transmitted Wavefront, RMS: $\lambda/14$
Diameter of Small Mirror (mm): 8.8
Working Distance (mm): 23.75
Aperture Diameter (mm): 8.5
Note: Entrance Pupil Position specification is measured in mm from flange
Coating Specification: R _{avg} >83% @ 150 - 1000nm (typical) R _{avg} >94% @ 1000 - 11000nm (typical)
Wavelength Range (nm): 150 - 11000
Style: Finite Conjugate
Manufacturer: Edmund Optics®
Flange Distance (mm): 150

Regulatory Compliance

RoHS: Not Compliant
Certificate of Conformance: View