

## FLIR T198533 USB Cable for EX Series



Stock #75-082 NEW **2 In Stock**

⊖ 1 ⊕ €64<sup>99</sup>

**ADD TO CART**

### Volume Pricing

|        |             |
|--------|-------------|
| Qty 1+ | €64,99 each |
|--------|-------------|

|            |                               |
|------------|-------------------------------|
| Need More? | <a href="#">Request Quote</a> |
|------------|-------------------------------|

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

#### General

ExSeries **Model Number:**

#### Regulatory Compliance

[View](#) **Certificate of Conformance:**

## Product Details

- Professional-Grade thermal Imagers for Industrial Applications
- Rugged, Handheld Design for Field Use
- Wide Temperature Ranges up to 550°C (1022°F)
- Wi-Fi for Fast Image Transfer and Reporting

The FLIR ExSeries delivers professional-grade thermal imaging in a rugged, handheld design built for demanding field environments. Offering industry-leading infrared resolution and wide temperature measurement ranges up to 550°C (1022°F), the E5 Pro, E6 Pro, and E8 Pro models are ideal for maintenance, building inspections, electrical diagnostics, HVAC servicing, and industrial troubleshooting. The E5 Pro (160 × 120 resolution) provides reliable thermal imaging for general inspections, the E6 Pro (240 × 180 resolution) offers enhanced resolution for identifying smaller temperature variations, and the E8 Pro (320 × 240 resolution) delivers the highest clarity and thermal sensitivity for advanced diagnostics. Built-in Wi-Fi connectivity allows for fast image transfer, reporting, and data sharing directly from the field, streamlining workflows and improving efficiency. With precision thermal sensitivity down to 0.04°C on the E8 Pro, users can detect subtle heat patterns and prevent equipment failures before they occur. The ExSeries combines FLIR's trusted infrared technology with durability and portability, making it a top choice for professional thermal imaging applications.

| Model               | E5 Pro                         | E6 Pro                           | E8 Pro                          |
|---------------------|--------------------------------|----------------------------------|---------------------------------|
| Resolution          | 160 × 120 (19,200 pixels)      | 240 × 180 pixels (43,200 pixels) | 160 × 120 (19,200 pixels)       |
| Temp Range          | -20°C to 400°C (-4°F to 752°F) | -20°C to 550°C (-4°F to 1022°F)  | -20°C to 550°C (-4°F to 1022°F) |
| Thermal sensitivity | <0.06°C                        | <0.05°C                          | <0.04°C                         |

**Accuracy:** ±2°C (±3.6°F) or ±2% of reading, for ambient temperature 10°C to 35°C (50°F to 95°F) and object temperature above 0°C (32°F)